


# STOLL

## Spare parts catalog

CMS ADF-3 (Typ 681)

Component type 002

E10 | E12 | E14 | E16 | E18 | E18m.16 | E12m.  
10 | E14/12 | E6.2 | E7.2 | E7.2 k&w | E8.2



Document no. 263797\_02\_EN

Release 2016/08



# 1 Introduction

## Imprint

All rights reserved.

The utilisation of texts and pictures, also in extracts, without our agreement is unfavourable to the copyright.

Our products are being developed further continuously. They are therefore subject to technical modifications.

The indications of this catalog are without liability.

©

H. Stoll AG & Co.KG

Stollweg 1

D-72760 Reutlingen, Germany

Phone: +49 (07121) 313-289

Fax: +49 (07121) 313-347

e-mail: spareparts@stoll.com

## Notes for the order

This catalog serves to order spare parts.

It can only be applied to the machine type recorded on the title page.





When ordering spare parts we imperatively ask for the following indications as otherwise a delivery of spare parts is not possible:

1. Type of machine, gauge, no. of machine.
2. Page no., designation, ID, quantity.

Only genuine STOLL spare parts may be used for repairs.

## 1.1 Search help

In order to make the search of the spare parts easier, the following elements will be used in the spare parts catalog:

| Symbol  | Meaning   |
|---|---|
| $\Sigma$  | Indicates an assembly   |
|    | Position indicator with the position number (X).                          |
|    | Indicates an element of another assembly.                                 |
|     | Indicates an assembly which is represented more detailed beside.          |
|    | Indicates an assembly which is represented on another page more detailed. |
|    | Screw torques (z) deviating from the preferential row.                    |
|    | Detail, represented enlarged in the direction of the arrow.               |
|    | Explosion representation, single elements enlarged.                       |
|   | Indicates a group of parts.   |
|  | Indicates the left side or view.  |
|  | Indicates the right-hand side or view.                                    |
|  | Indicates a sectional drawing or a view in the viewing direction.         |

## 1.2 Torques

### Preferential row of screw torques

- Torques are **valid** for:  
Connection steel-steel, black, phosphatized, galvanized, rolled or cut thread as well as only for plain (head) supports.
- Torques are **not valid** for:  
protected screws with: lock washers, rib heads, coated and clamping screws and nuts. They are also not used for self-cutting threads.
- Torques differing from this preferential row of torques must be taken from the corresponding location in the drawings.

| <b>Drehmomente</b><br><b>Torques</b><br><b>Couples</b><br><b>Coppias</b><br><b>Momentos de rotación</b><br>[Nm] ± 10 % (für $\mu_{ges} = 0,12$ ) |     | Festigkeitsklassen    |            |            |
|--|-----|-----------------------|------------|------------|
|  |     | Property class        |            |            |
|  |     | Classes de résistance |            |            |
|  |     | Classi di resistenza  |            |            |
|  |     | Clasas de resistencia |            |            |
|  |     | 4,8                   | 8,8        | 12,9       |
| Regelgewinde<br>Coarse-pitch thread<br>Filetage à pas gros<br>Filetto regolatore<br>Filete regulador   | M3  | <b>0,6</b>            | <b>1,2</b> | <b>2,5</b> |
|  | M4  | <b>1,2</b>            | <b>2,5</b> | <b>5</b>   |
|  | M5  | <b>2,5</b>            | <b>5</b>   | <b>9</b>   |
|  | M6  | <b>5</b>              | <b>9</b>   | <b>18</b>  |
|  | M8  |                       | <b>18</b>  | <b>40</b>  |
|  | M10 |                       | <b>40</b>  |            |
|  | M12 |                       | <b>80</b>  |            |



# Table of Contents


|          |  |           |
|----------|--|-----------|
| <b>1</b> | <b>Introduction .....</b>                                  | <b>3</b>  |
| 1.1      | Search help .....  | 4         |
| 1.2      | Torques .....  | 5         |
| <b>2</b> | <b>Carriage drive .....</b>                                | <b>11</b> |
| 2.1      | Main drive .....   | 12        |
| 2.1.1    | Motor and belt drive .....                                 | 13        |
| 2.1.2    | Bearing .....  | 14        |
| 2.2      | Energy chains .....  | 15        |
| <b>3</b> | <b>Racking .....</b>                                       | <b>17</b> |
| 3.1      | Racking .....  | 18        |
| <b>4</b> | <b>Needle beds .....</b>                                   | <b>19</b> |
| 4.1      | Needle bed E10 .....                                       | 20        |
| 4.1.1    | Continuation needle bed E10 .....                          | 21        |
| 4.2      | Needle bed E12 .....                                       | 22        |
| 4.2.1    | Continuation needle bed E12 .....                          | 23        |
| 4.3      | Needle bed E14 .....                                       | 24        |
| 4.3.1    | Continuation needle bed E14 .....                          | 25        |
| 4.4      | Needle bed E16 .....                                       | 26        |
| 4.4.1    | Continuation needle bed E16 .....                          | 27        |
| 4.5      | Needle bed E18 .....                                       | 28        |
| 4.5.1    | Continuation needle bed E18 .....                          | 29        |
| 4.6      | Needle bed E12m.10 .....                                   | 30        |
| 4.6.1    | Continuation needle bed E12m.10 .....                      | 31        |
| 4.7      | Needle bed E18m.16 .....                                   | 32        |
| 4.7.1    | Continuation needle bed E18m.16 .....                      | 33        |
| 4.8      | Needle bed E14/12 .....                                    | 34        |
| 4.8.1    | Continuation needle bed E14/12 .....                       | 35        |
| 4.9      | Needle bed E6.2 .....                                      | 36        |
| 4.9.1    | Continuation needle bed E6.2 .....                         | 37        |
| 4.10     | Needle bed E7.2 .....                                      | 38        |
| 4.10.1   | Continuation needle bed E7.2 .....                         | 39        |
| 4.11     | Needle bed E7.2 k&w .....                                  | 40        |
| 4.11.1   | Continuation needle bed E7.2 k&w .....                     | 41        |
| 4.12     | Needle bed E8.2 .....                                      | 42        |
| 4.12.1   | Continuation needle bed E8.2 .....                         | 43        |
| 4.13     | Needle beds, fixing elements .....                         | 44        |
| 4.14     | Right clamping and cutting bed E10 E12 E14 E6.2 E7.2 ..... | 45        |
| 4.15     | Left clamping and cutting bed E10 E12 E14 E6.2 E7.2 .....  | 46        |
| 4.16     | Right clamping and cutting bed E16 E18 E8.2 .....          | 47        |
| 4.17     | Left clamping and cutting bed E16 E18 E8.2 .....           | 48        |
| <b>5</b> | <b>Carriage .....</b>                                      | <b>49</b> |
| 5.1      | Carriage and linear guidance .....                         | 50        |
| 5.2      | Carriage front and rear .....                              | 51        |
| 5.3      | Carriage parts .....                                       | 52        |
| 5.4      | Continuation of carriage parts .....                       | 53        |
| 5.5      | Brush holder .....   | 54        |
| 5.6      | Needle detector .....                                      | 55        |
| 5.7      | Holding-down jack control .....                            | 56        |
| 5.8      | Grease supply .....  | 57        |
| 5.9      | Cam box E10 .....  | 58        |
| 5.9.1    | Cams E10 .....   | 59        |
| 5.10     | Cam box E12 .....  | 60        |
| 5.10.1   | Cams E12 .....   | 61        |
| 5.11     | Cam box E14 E14/12 .....                                   | 62        |
| 5.11.1   | Cams E14 E14/12 .....                                      | 63        |

|           |  |            |
|-----------|--|------------|
| 5.12      | Cam box E16 E18 E18m.16 .....                      | 64         |
| 5.12.1    | Cams E16 E18 E18m.16 .....                         | 65         |
| 5.13      | Cam box E12m.10 .....                              | 66         |
| 5.13.1    | Cams E12m.10 .....                                 | 67         |
| 5.14      | Cam box E6.2 .....                                 | 68         |
| 5.14.1    | Cams E6.2 .....                                    | 69         |
| 5.15      | Cam box E7.2 .....                                 | 70         |
| 5.15.1    | Cams E7.2 .....                                    | 71         |
| 5.16      | Cam box E7.2 k&w .....                             | 72         |
| 5.16.1    | Cams E7.2 k&w .....                                | 73         |
| 5.17      | Cam box E8.2 .....                                 | 74         |
| 5.17.1    | Cams E8.2 .....                                    | 75         |
| <b>6</b>  | <b>Main take-down .....</b>                        | <b>77</b>  |
| 6.1       | Main Take-down .....                               | 78         |
| 6.2       | Main take-down on the left .....                   | 79         |
| 6.3       | Main take-down on the right .....                  | 80         |
| 6.3.1     | Mounting plate .....                               | 81         |
| 6.3.2     | Full floating axle on the left and the right ..... | 82         |
| 6.4       | Main take-down in the middle .....                 | 83         |
| 6.4.1     | Stripper angle .....                               | 84         |
| 6.4.2     | Rear take-down roller .....                        | 85         |
| 6.4.3     | Front take-down roller .....                       | 86         |
| 6.4.4     | Impulse sensor and motor .....                     | 89         |
| <b>7</b>  | <b>Auxiliary Take-down .....</b>                   | <b>91</b>  |
| 7.1       | Auxiliary take-down pre-assembled .....            | 92         |
| 7.1.1     | Right bearing of the auxiliary take-down .....     | 93         |
| 7.1.2     | Left bearing of the auxiliary take-down .....      | 94         |
| 7.1.3     | Metal angle on the left and right complete .....   | 95         |
| 7.2       | Auxiliary take-down in the middle .....            | 96         |
| 7.3       | Motor .....  | 97         |
| 7.4       | Yarn brake at clamping and cutting bed .....       | 98         |
| <b>8</b>  | <b>Comb Take-down .....</b>                        | <b>99</b>  |
| 8.1       | Comb Take-down .....                               | 100        |
| 8.2       | Comb take-down on the left .....                   | 101        |
| 8.3       | Comb take-down on the right .....                  | 102        |
| 8.3.1     | Drive shaft of comb .....                          | 103        |
| 8.3.2     | Swivel lever comb take-down .....                  | 104        |
| 8.4       | Comb take-down in the middle .....                 | 105        |
| 8.4.1     | Comb unit .....                                    | 106        |
| 8.4.2     | Switching lever comb take-down .....               | 107        |
| <b>9</b>  | <b>Belt Take-Down .....</b>                        | <b>109</b> |
| 9.1       | Belt Take-Down .....                               | 110        |
| 9.2       | Belt .....   | 111        |
| 9.3       | Drive unit .....                                   | 112        |
| 9.4       | Support on the left .....                          | 113        |
| 9.5       | Winding guard .....                                | 114        |
| 9.6       | Yarn brakes .....                                  | 115        |
| <b>10</b> | <b>Yarn delivery device .....</b>                  | <b>117</b> |
| 10.1      | Drive unit yarn carrier complete .....             | 118        |
| 10.2      | YC rail, drive of operating shaft .....            | 119        |
| 10.3      | YC rail, drive .....                               | 120        |
| 10.4      | Yarn carrier rails and carriages .....             | 121        |
| 10.5      | Yarn guide system with 32 FKE ADF .....            | 122        |
| 10.5.1    | Yarn control unit ADF .....                        | 123        |
| <b>11</b> | <b>Fluff absorption .....</b>                      | <b>125</b> |
| 11.1      | Fluff absorption .....                             | 126        |
| 11.2      | Fluff absorption, carriage parts .....             | 127        |

|           |  |            |
|-----------|--|------------|
| <b>12</b> | <b>Operation and control</b>                       | <b>129</b> |
| 12.1      | Starting device                                    | 130        |
| 12.1.1    | Bearing of the engaging rod                        | 131        |
| 12.2      | Input unit   | 132        |
| 12.3      | Control of Collecting Area                         | 133        |
| 12.4      | Signal light                                       | 134        |
| 12.5      | Shock stop motion E10 E12 E14 E6.2 E7.2            | 135        |
| 12.6      | Shock stop motion E16 18 E8.2                      | 136        |
| 12.7      | Measuring device                                   | 137        |
| <b>13</b> | <b>Protective devices</b>                          | <b>139</b> |
| 13.1      | Lateral safety doors                               | 140        |
| 13.2      | Panelling  | 141        |
| 13.3      | Covers   | 142        |
| 13.4      | Light curtain                                      | 143        |
| 13.5      | Left table   | 144        |
| 13.6      | Right table  | 145        |
| 13.7      | Table left and right, rollers                      | 146        |
| <b>14</b> | <b>Electrical equipment</b>                        | <b>147</b> |
| 14.1      | Circuit diagram (222) as PDF                       | 149        |
| 14.2      | Cable guide front and rear ADF                     | 150        |
| 14.3      | Cable set installation                             | 151        |
| 14.3.1    | Cable set base 1 AFDF                              | 152        |
| 14.3.2    | Loom of cables base 2 AFDF                         | 153        |
| 14.3.3    | Loom of cables 5XX ADF                             | 154        |
| 14.3.4    | Loom of cables comb                                | 155        |
| 14.4      | Loom of cables servo AFDF left 32-fold             | 156        |
| 14.5      | Loom of cables servo AFDF right 32-fold            | 157        |
| <b>15</b> | <b>Control electronics</b>                         | <b>159</b> |
| 15.1      | Right control cabinet                              | 160        |
| 15.2      | Left control cabinet                               | 161        |
| <b>16</b> | <b>Deliverable accessories</b>                     | <b>163</b> |
| 16.1      | Accessories part 1                                 | 164        |
| 16.2      | Accessories part 2                                 | 165        |
| <b>17</b> | <b>Special attachments</b>                         | <b>167</b> |
| 17.1      | Lateral yarn feeding                               | 168        |
| 17.1.1    | Safety door on the left                            | 169        |
| 17.1.2    | Safety door on the right                           | 170        |
| 17.1.3    | Left yarn guide                                    | 171        |
| 17.1.4    | Right yarn guide                                   | 172        |
| 17.1.5    | Friction feed wheel complete                       | 173        |
| 17.2      | Storage feed wheel MSF-3 ADF                       | 174        |
| 17.3      | Yarn length measuring device on the left complete  | 175        |
| 17.3.1    | Yarn length measuring device                       | 176        |
| 17.4      | Yarn length measuring device on the right complete | 177        |
| 17.4.1    | Yarn length measuring device on the right          | 178        |
| 17.5      | Yarn brake   | 179        |
| 17.6      | Adjusting plates                                   | 180        |




## 2 Carriage drive




## 2.1 Main drive

| Pos      | Designation                  | ID             | Pos | Designation                   | ID      |
|----------|------------------------------|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Main drive complete</b>   | <b>258 061</b> | 7   | Protective plate on the right | 263 630 |
| 1        | Drive unit complete          | 265 323        | 500 | Cap screw M12x30              | 023 660 |
| 2        | Bearing                      | 265 339        | 501 | Setscrew M8x35                | 257 945 |
| 3        | Toothed belt 50AT10/5040     | 257 984        | 502 | Cap screw M8x25               | 020 142 |
| 4        | Support of buffer            | 257 947        | 503 | Cap screw M12x25              | 023 383 |
| 5        | Parabolic spring             | 258 009        | 506 | Washer 12                     | 020 875 |
| 6        | Protective plate on the left | 263 602        | 507 | Pan head screw M5x8           | 239 408 |




## 2.1.1 Motor and belt drive

| Pos      | Designation                | Id             | Pos | Designation                   | Id      |
|----------|----------------------------|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Drive unit complete</b> | <b>265 323</b> | 522 | Grooved ball bearing 6306-2RS | 257 916 |
| 1        | Drive unit                 | 264 336        | 523 | Retaining ring68x2.5          | 022 914 |
| 2        | Drive bearing              | 265 324        | 3   | Toothed belt250 HP-S5M 920 NG | 258 010 |
| 21       | Drive bearing              | 257 896        | 4   | Fan complete                  | 253 692 |
| 22       | Drive shaft                | 265 321        | 500 | Pan-head screw M10X25         | 023 684 |
| 23       | Pinion57 AT10 18           | 265 430        | 501 | Hexagon screw M6x25           | 257 917 |
| 24       | Timing belt pulley         | 257 948        | 502 | Disk10,5X25X2,5               | 022 178 |
| 520      | Tension set 22x40          | 258 040        | 503 | Pan-head screw M6X10          | 023 183 |
| 521      | Tension set 35X60          | 258 039        | 504 | Setscrew M8x35                | 257 945 |




## 2.1.2 Bearing

| Pos      | Designation     | Id             | Pos | Designation                   | Id      |
|----------|-----------------|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Bearing</b>  | <b>265 339</b> |     |                               |         |
| 1        | Tension bearing | 257 915        | 500 | Tension set 22x40             | 258 040 |
| 2        | Drive shaft     | 265 321        | 501 | Grooved ball bearing 6306-2RS | 257 916 |
| 3        | Roll            | 265 322        | 502 | Retaining ring 68x2,5         | 022 914 |




## 2.2 Energy chains

| Pos      | Designation                  | ID      | Pos | Designation             | ID      |
|----------|------------------------------|---------|-----|-------------------------|---------|
| <b>Σ</b> | <b>Energy chains</b>         |         | 6   | Front depositing gutter | 265 577 |
| 1        | Cable driver (front)         | 265 343 | 7   | Deposit gutter          | 265 545 |
| 2        | Cable driver (rear)          | 265 473 | 8   | Rear depositing gutter  | 265 340 |
| 3        | Energy chain E6.35.050.100.0 | 265 716 | 500 | Cap screw M5x12         | 020 132 |
| 4        | Cable holder front           | 266 666 | 506 | Cap screw M6x25         | 020 137 |
| 5        | Cable holder rear            | 266 667 | 507 | Pan-head screw M6x10    | 023 183 |






### 3 Racking




### 3.1 Racking

| Pos      | Designation                | Id      | Pos | Designation          | Id      |
|----------|----------------------------|---------|-----|----------------------|---------|
| <b>Σ</b> | <b>Racking</b>             |         |     |                      |         |
| 1        | Racking motor OKC complete | 258 192 | 504 | Cap screw M8x25      | 020 142 |
| 2        | Bearing                    | 263 864 | 505 | Washer 8,4X20X3      | 022 175 |
| 3        | Spindle bearing            | 253 262 | 509 | Shim 0,03x15x85      | 023 162 |
| 4        | Card racking limit switch  | 229 396 | 510 | Shim 0,05x15x85      | 023 163 |
| 5        | Racking cover plate        | 258 634 | 511 | Shim 0,1x15x85       | 023 164 |
| 6        | Racking strip on the left  | 240 696 | 512 | Shim 0,2x15x85       | 023 170 |
| 7        | Racking strip              | 240 690 | 518 | Shim 0,03x15x75      | 023 395 |
| 8        | Guide strip                | 206 382 | 519 | Shim 0,05x15x75      | 023 396 |
| 9        | Toothed belt 150 S 5M 490  | 229 281 | 520 | Shim 0,1x15x75       | 023 397 |
| 13       | Switch plate               | 240 722 | 521 | Shim 0,2x15x75       | 023 398 |
| 19       | Stop screw                 | 221 386 | 900 | Cap screw M6x12      | 022 795 |
| 501      | Cap screw M6x16            | 271 322 | 901 | Pan head screw M6x10 | 023 183 |
| 503      | Pan head screw M6x10       | 023 183 | 902 | Cap screw M8x30      | 020 143 |




## 4 Needle beds




## 4.1 Needle bed E10

| Pos      | Designation  | Id             | Pos  | Designation                 | Id      |
|----------|--|----------------|------|-----------------------------|---------|
| <b>Σ</b> | <b>Needle bed complete at the front + rear E10</b> | <b>263 860</b> | 17   | Needle bar on the right     | 213 999 |
| 1        | Needle bed at the front + rear E10                 | 263 709        | 18   | Cover rail at the rear      | 213 981 |
| 2        | Holding-down jack bed at the rear E10              | 240 447        | 19   | Cover rail at the front E10 | 214 036 |
| 3        | Holding-down jack bed at the front E10             | 240 430        | 20   | Cover rail                  | 213 762 |
| 41       | Needle E10 with round hook                         | 205 398        | 21   | Cover rail                  | 213 763 |
| 42       | Coupling part E10-12                               | 253 382        | 22   | Locating wire D=2,8 1290mm  | 213 983 |
| 50       | Intermediate slider with brake E10-12              | 255 535        | 500  | Cap screw M5x10             | 022 918 |
| 61       | Selection jack E10-12                              | 200 688        | 503  | Cap screw M5x22             | 023 193 |
| 62       | Selector spring E10-12                             | 200 691        | 40*  | Disk brush                  | 235 612 |
| 7        | Knock-over bit E10                                 | 239 756        | 42*  | Disk brush                  | 202 600 |
| 8        | Holding-down jack (trick wall) E10                 | 239 815        | 43*  | Adjusting bolt              | 251 772 |
| 16       | Needle bar on the left                             | 213 998        | 540* | Cap screw M5x12             | 020 032 |




## 4.1.1 Continuation needle bed E10

| Pos | Designation                                | Id      | Pos | Designation          | Id      |
|-----|--|---------|-----|----------------------|---------|
| 2   | Spring steel wire $\varnothing 0,6$ E10-14 | 213 990 | 502 | Cap screw M5x8       | 023 154 |
| 3   | Spring steel wire $\varnothing 2,0$        | 213 996 | 504 | Springy thrust piece | 023 177 |
| 14  | Limiters on the left E10-14                | 205 764 | 507 | Shim0,05x18,5x34     | 023 196 |
| 15  | Limiters on the right E10-14               | 205 765 | 508 | Shim0,1x18,5x34      | 023 197 |
| 22  | Locating wire $\varnothing 2,8$            | 213 983 | 509 | Shim0,2x18,5x34      | 023 253 |




## 4.2 Needle bed E12

| Pos      | Designation  | Id             | Pos  | Designation                 | Id      |
|----------|--|----------------|------|-----------------------------|---------|
| $\Sigma$ | <b>Needle bed complete at the front + rear E12</b> | <b>263 861</b> |      |                             |         |
| 1        | Needle bed at the front + rear E12                 | 263 710        | 18   | Cover rail at the rear      | 213 981 |
| 3        | Main trick wall E12                                | 260 343        | 19   | Cover rail at the front E12 | 214 037 |
| 4        | Pressure slide E10-14                              | 213 919        | 20   | Cover rail                  | 213 762 |
| 6        | Spring steel wire $\varnothing 2,0$                | 213 996        | 21   | Cover rail                  | 213 763 |
| 71       | Needle E12   | 204 009        | 24   | Bush                        | 206 090 |
| 72       | Coupling part E10-12                               | 253 382        | 26   | Stop screw                  | 235 244 |
| 81       | Intermediate slider with brake E10-12              | 255 535        | 500  | Cap screw M6x14             | 022 658 |
| 91       | Selection jack E10-12                              | 200 688        | 502  | Cap screw M5x8              | 023 379 |
| 92       | Selector spring E10-12                             | 200 691        | 503  | Cap screw M5x22             | 023 193 |
| 10       | Holding-down jack bed at the rear E12              | 240 448        | 505  | Setscrew M3,5x3-1           | 020 512 |
| 11       | Holding-down jack bed at the front E12             | 240 431        | 40*  | Disk brush                  | 235 612 |
| 12       | Knock-over bit E12                                 | 259 212        | 41*  | Container disk brush        | 233 012 |
| 13       | Holding-down jack (trick wall) E12                 | 259 213        | 42*  | Disk brush                  | 202 600 |
| 16       | Needle bar on the left                             | 213 998        | 43*  | Adjusting bolt              | 251 772 |
| 17       | Needle bar on the right                            | 213 999        | 540* | Cap screw M5x12             | 020 032 |




## 4.2.1 Continuation needle bed E12

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 2   | Locating wire $\varnothing 3,4$     | 213 995 | 503 | Cap screw M5x22      | 023 193 |
| 5   | Spring steel wire $\varnothing 0,6$ | 213 990 | 504 | Cap screw M5x12      | 022 943 |
| 6   | Spring steel wire $\varnothing 2,0$ | 213 996 | 506 | Springy thrust piece | 023 177 |
| 14  | Limiters on the left E10-E14        | 205 764 | 509 | Shim0,05x18,5x34     | 023 196 |
| 15  | Limiters on the right E10-E14       | 205 765 | 510 | Shim0,1x18,5x34      | 023 197 |
| 22  | Locating wire $\varnothing 2,8$     | 213 983 | 511 | Shim0,2x18,5x34      | 023 253 |
| 501 | Cap screw M5x8                      | 023 154 |     |                      |         |





## 4.3 Needle bed E14

| Pos      | Designation  | Id             | Pos  | Designation                 | Id      |
|----------|--|----------------|------|-----------------------------|---------|
| $\Sigma$ | <b>Needle bed complete at the front + rear E14</b> | <b>263 878</b> |      |                             |         |
| 1        | Needle bed at the front + rear E14                 | 263 711        | 19   | Cover rail at the rear      | 213 981 |
| 3        | Main trick wall E14                                | 260 344        | 20   | Cover rail at the front E14 | 214 038 |
| 4        | Pressure slide E10-14                              | 213 919        | 21   | Cover rail                  | 213 762 |
| 6        | Spring steel wire $\varnothing 2,0$                | 213 996        | 22   | Cover rail                  | 213 763 |
| 71       | Needle E14   | 209 614        | 25   | Bush                        | 206 090 |
| 72       | Coupling part E14                                  | 253 383        | 27   | Stop screw                  | 235 244 |
| 81       | Intermediate slider with brake E14                 | 255 536        | 502  | Cap screw M5x8              | 023 379 |
| 10       | Selection jack with spring E14                     | 224 725        | 503  | Cap screw M5x22             | 023 193 |
| 11       | Holding-down jack bed at the rear E14              | 240 449        | 505  | Setscrew M3,5x3             | 020 512 |
| 12       | Holding-down jack bed at the front E14             | 240 432        | 40*  | Disk brush                  | 235 612 |
| 13       | Knock-over bit E14                                 | 209 649        | 41*  | Container disk brush        | 233 012 |
| 14       | Holding-down jack trick wall E14                   | 235 262        | 42*  | Disk brush                  | 202 600 |
| 17       | Needle bar on the left                             | 213 998        | 43*  | Adjusting bolt              | 251 772 |
| 18       | Needle bar on the right                            | 213 999        | 540* | Cap screw M5x12             | 020 032 |




4.3.1 Continuation needle bed E14

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 2   | Locating wire $\varnothing 3,4$     | 213 995 | 503 | Cap screw M5x22      | 023 193 |
| 5   | Spring steel wire $\varnothing 0,6$ | 213 990 | 504 | Cap screw M5x12      | 022 943 |
| 6   | Spring steel wire $\varnothing 2,0$ | 213 996 | 506 | Springy thrust piece | 023 177 |
| 15  | Limiters on the left E10-14         | 205 764 | 509 | Shim0,05x18,5x34     | 023 196 |
| 16  | Limiters on the right E10-14        | 205 765 | 510 | Shim0,1x18,5x34      | 023 197 |
| 23  | Locating wire $\varnothing 2,8$     | 213 983 | 511 | Shim0,2x18,5x34      | 023 253 |
| 501 | Cap screw M5x8                      | 023 154 |     |                      |         |




### 4.4 Needle bed E16

| Pos      | Designation  | Id             | Pos  | Designation                                       | Id      |
|----------|--|----------------|------|---|---------|
| <b>Σ</b> | <b>Needle bed complete at the front + rear E16</b> | <b>263 862</b> |      |   |         |
| 1        | Needle bed at the front + rear E16                 | 263 712        | 19   | Cover rail at the front E16                       | 222 531 |
| 3        | Main trick wall E16                                | 245 319        | 20   | Cover rail  | 213 762 |
| 4        | Pressure strip at the front E5-14                  | 219 536        | 21   | Cover rail  | 213 763 |
| 6a       | Needle E16   | 232 243        | 24   | Bush  | 206 090 |
| 6b       | Coupling part E16-20                               | 253 384        | 26   | Spring steel wire D=2,0 1287 mm                   | 213 996 |
| 7        | Pressure strip at the rear E5-14                   | 219 537        | 27   | Pressure strip at the rear on the right E16 – E20 | 223 042 |
| 8        | Intermediate slider with brake E16-18              | 255 537        | 28   | Stop screw  | 235 244 |
| 9        | Selection jack E16-20                              | 222 265        | 501  | Cap screw M4-M5x8                                 | 023 379 |
| 10       | Holding-down jack bed at the rear E16              | 240 450        | 502  | Cap screw M5x22                                   | 023 193 |
| 11       | Holding-down jack bed at the front E16             | 240 433        | 504  | Setscrew M3,5x3-1                                 | 020 512 |
| 12       | Knock-over bit wire position E16                   | 261 865        | 40*  | Disk brush  | 235 612 |
| 13       | Holding-down jack E16                              | 264 106        | 41*  | Container disk brush                              | 233 012 |
| 16       | Needle bar on the left                             | 213 998        | 42*  | Disk brush  | 202 600 |
| 17       | Needle bar on the right                            | 213 999        | 43*  | Adjusting bolt                                    | 251 772 |
| 18       | Cover rail at the rear                             | 213 981        | 540* | Cap screw M5x12                                   | 020 032 |




## 4.4.1 Continuation needle bed E16

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 2   | Locating wire $\varnothing 3,4$     | 213 995 | 502 | Cap screw M5x22      | 023 193 |
| 5   | Spring steel wire $\varnothing 0,5$ | 220 759 | 503 | Cap screw M5x12-8.8  | 022 943 |
| 14  | Limitier on the left E16-20         | 220 821 | 505 | Springy thrust piece | 023 177 |
| 15  | Limitier on the right E16-20        | 220 822 | 508 | Shim0,05x18,5x34     | 023 196 |
| 22  | Locating wire $\varnothing 2,8$     | 223 922 | 509 | Shim0,1x18,5x34      | 023 197 |
| 26  | Spring steel wire $\varnothing 2,0$ | 213 996 | 510 | Shim0,2X18,5X34      | 023 253 |




## 4.5 Needle bed E18

| Pos      | Designation  | Id             | Pos  | Designation                                       | Id      |
|----------|--|----------------|------|---|---------|
| $\Sigma$ | <b>Needle bed complete at the front + rear E18</b> | <b>263 884</b> |      |   |         |
| 1        | Needle bed at the front + rear E18                 | 263 713        | 19   | Cover rail at the front E18                       | 220 745 |
| 3        | Main trick wall E18                                | 251 051        | 20   | Cover rail  | 213 762 |
| 4        | Pressure strip at the front E5-14                  | 219 536        | 21   | Cover rail  | 213 763 |
| 6a       | Needle E18   | 239 527        | 24   | Bush  | 206 090 |
| 6b       | Coupling part E16-20                               | 253 384        | 26   | Spring steel wire D=2,0 1287 mm                   | 213 996 |
| 7        | Pressure strip at the rear E5-14                   | 219 537        | 27   | Pressure strip at the rear on the right E16 – E20 | 223 042 |
| 8        | Intermediate slider with brake E16-18              | 255 537        | 28   | Stop screw  | 235 244 |
| 9        | Selection jack E16-20                              | 222 265        | 501  | Cap screw M5x8                                    | 023 379 |
| 10       | Holding-down jack bed at the rear E18              | 240 451        | 502  | Cap screw M5x22                                   | 023 193 |
| 11       | Holding-down jack bed at the front E18             | 240 434        | 504  | Setscrew M3,5x3-1                                 | 020 512 |
| 12       | Knock-over bit wire position 0,8 mm                | 263 927        | 40*  | Disk brush  | 235 612 |
| 13       | Holding-down jack E18                              | 264 107        | 41*  | Container disk brush                              | 233 012 |
| 16       | Needle bar on the left                             | 213 998        | 42*  | Disk brush  | 202 600 |
| 17       | Needle bar on the right                            | 213 999        | 43*  | Adjusting bolt                                    | 251 772 |
| 18       | Cover rail at the rear                             | 213 981        | 540* | Cap screw M5x12                                   | 020 032 |




## 4.5.1 Continuation needle bed E18

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 2   | Locating wire $\varnothing 3,4$     | 213 995 | 502 | Cap screw M5x22      | 023 193 |
| 5   | Spring steel wire $\varnothing 0,5$ | 220 759 | 503 | Cap screw M5x12-8.8  | 022 943 |
| 14  | Limiters on the left E16-20         | 220 821 | 505 | Springy thrust piece | 023 177 |
| 15  | Limiters on the right E16-20        | 220 822 | 508 | Shim0,05x18,5x34     | 023 196 |
| 22  | Locating wire $\varnothing 2,8$     | 223 922 | 509 | Shim0,1x18,5x34      | 023 197 |
| 26  | Spring steel wire $\varnothing 2,0$ | 213 996 | 510 | Shim0,2x18,5x34      | 023 253 |




## 4.6 Needle bed E12m.10

| Pos      | Designation  | Id             | Pos  | Designation                 | Id      |
|----------|--|----------------|------|-----------------------------|---------|
| $\Sigma$ | <b>Needle bed complete at the front + rear E12m.10</b> | <b>263 876</b> |      |                             |         |
| 1        | Needle bed at the front + rear E12                     | 263 710        | 18   | Cover rail at the rear      | 213 981 |
| 3        | Main trick wall E12                                    | 260 343        | 19   | Cover rail at the front E12 | 214 037 |
| 4        | Pressure slide E10-14                                  | 213 919        | 20   | Cover rail                  | 213 762 |
| 6        | Spring steel wire $\varnothing 2,0$                    | 213 996        | 21   | Cover rail                  | 213 763 |
| 71       | Needle E10 with round hook                             | 205 398        | 24   | Bush                        | 206 090 |
| 72       | Coupling part E10-12                                   | 253 382        | 26   | Stop screw                  | 235 244 |
| 81       | Intermediate slider with brake E10-12                  | 255 535        | 500  | Cap screw M6x14             | 022 658 |
| 91       | Selection jack E10-12                                  | 200 688        | 502  | Cap screw M5x8              | 023 379 |
| 92       | Selector spring E10-12                                 | 200 691        | 503  | Cap screw M5x22             | 023 193 |
| 10       | Holding-down jack bed at the rear E12                  | 240 448        | 505  | Setscrew M3,5x3-1           | 020 512 |
| 11       | Holding-down jack bed at the front E12                 | 240 431        | 40*  | Disk brush                  | 235 612 |
| 12       | Knock-over bit E12                                     | 259 212        | 41*  | Container disk brush        | 233 012 |
| 13       | Holding-down jack (trick wall) E12                     | 259 213        | 42*  | Disk brush                  | 202 600 |
| 16       | Needle bar on the left                                 | 213 998        | 43*  | Adjusting bolt              | 251 772 |
| 17       | Needle bar on the right                                | 213 999        | 540* | Cap screw M5x12             | 020 032 |




## 4.6.1 Continuation needle bed E12m.10

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 2   | Locating wire $\varnothing 3,4$     | 213 995 | 503 | Cap screw M5x22      | 023 193 |
| 5   | Spring steel wire $\varnothing 0,6$ | 213 990 | 504 | Cap screw M5x12      | 022 943 |
| 6   | Spring steel wire $\varnothing 2,0$ | 213 996 | 506 | Springy thrust piece | 023 177 |
| 14  | Limiters on the left E10-E14        | 205 764 | 509 | Shim0,05x18,5x34     | 023 196 |
| 15  | Limiters on the right E10-E14       | 205 765 | 510 | Shim0,1x18,5x34      | 023 197 |
| 22  | Locating wire $\varnothing 2,8$     | 213 983 | 511 | Shim0,2X18,5X34      | 023 253 |
| 501 | Cap screw M5x8                      | 023 154 |     |                      |         |




## 4.7 Needle bed E18m.16

| Pos      | Designation  | Id             | Pos  | Designation                                       | Id      |
|----------|--|----------------|------|---|---------|
| $\Sigma$ | <b>Needle bed complete at the front + rear E18m.16</b> | <b>266 583</b> |      |   |         |
| 1        | Needle bed at the front + rear E18                     | 263 713        | 19   | Cover rail at the front E18                       | 220 745 |
| 3        | Main trick wall E18                                    | 251 051        | 20   | Cover rail  | 213 762 |
| 4        | Pressure strip at the front E5-14                      | 219 536        | 21   | Cover rail  | 213 763 |
| 6a       | Needle E16   | 232 243        | 24   | Bush  | 206 090 |
| 6b       | Coupling part E16-20                                   | 253 384        | 26   | Spring steel wire D=2,0 1287 mm                   | 213 996 |
| 7        | Pressure strip at the rear E5-14                       | 219 537        | 27   | Pressure strip at the rear on the right E16 – E20 | 223 042 |
| 8        | Intermediate slider with brake E16-18                  | 255 537        | 28   | Stop screw  | 235 244 |
| 9        | Selection jack E16-20                                  | 222 265        | 501  | Cap screw M5x8                                    | 023 379 |
| 10       | Holding-down jack bed at the rear E18                  | 240 451        | 502  | Cap screw M5x22                                   | 023 193 |
| 11       | Holding-down jack bed at the front E18                 | 240 434        | 504  | Setscrew M3,5x3-1                                 | 020 512 |
| 12       | Knock-over bit wire position 0,8 mm                    | 263 927        | 40*  | Disk brush  | 235 612 |
| 13       | Holding-down jack E18                                  | 264 107        | 41*  | Container disk brush                              | 233 012 |
| 16       | Needle bar on the left                                 | 213 998        | 42*  | Disk brush  | 202 600 |
| 17       | Needle bar on the right                                | 213 999        | 43*  | Adjusting bolt                                    | 251 772 |
| 18       | Cover rail at the rear                                 | 213 981        | 540* | Cap screw M5x12                                   | 020 032 |




## 4.7.1 Continuation needle bed E18m.16

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 2   | Locating wire $\varnothing 3,4$     | 213 995 | 502 | Cap screw M5x22      | 023 193 |
| 5   | Spring steel wire $\varnothing 0,5$ | 220 759 | 503 | Cap screw M5x12-8.8  | 022 943 |
| 14  | Limiters on the left E16-20         | 220 821 | 505 | Springy thrust piece | 023 177 |
| 15  | Limiters on the right E16-20        | 220 822 | 508 | Shim0,05x18,5x34     | 023 196 |
| 22  | Locating wire $\varnothing 2,8$     | 223 922 | 509 | Shim0,1x18,5x34      | 023 197 |
| 26  | Spring steel wire $\varnothing 2,0$ | 213 996 | 510 | Shim0,2x18,5x34      | 023 253 |





## 4.8 Needle bed E14/12

| Pos      | Designation   | Id             | Pos  | Designation                 | Id      |
|----------|---|----------------|------|-----------------------------|---------|
| <b>Σ</b> | <b>Needle bed complete at the front + rear E14/12</b> | <b>263 880</b> |      |                             |         |
| 1        | Needle bed at the front + rear E14                    | 263 711        | 19   | Cover rail at the rear      | 213 981 |
| 3        | Main trick wall E14                                   | 260 344        | 20   | Cover rail at the front E14 | 214 038 |
| 4        | Pressure slide E10-14                                 | 213 919        | 21   | Cover rail                  | 213 762 |
| 6        | Spring steel wire $\varnothing 2,0$                   | 213 996        | 22   | Cover rail                  | 213 763 |
| 71       | Needle E14/12   | 227 756        | 25   | Bush                        | 206 090 |
| 72       | Coupling part E14                                     | 253 383        | 27   | Stop screw                  | 235 244 |
| 81       | Intermediate slider with brake E14                    | 255 536        | 502  | Cap screw M5x8              | 023 379 |
| 10       | Selection jack with spring E14                        | 224 725        | 503  | Cap screw M5x22             | 023 193 |
| 11       | Holding-down jack bed at the rear E14                 | 240 449        | 505  | Setscrew M3,5x3             | 020 512 |
| 12       | Holding-down jack bed at the front E14                | 240 432        | 40*  | Disk brush                  | 235 612 |
| 13       | Knock-over bit E14                                    | 209 649        | 41*  | Container disk brush        | 233 012 |
| 14       | Holding-down jack trick wall E14                      | 235 262        | 42*  | Disk brush                  | 202 600 |
| 17       | Needle bar on the left                                | 213 998        | 43*  | Adjusting bolt              | 251 772 |
| 18       | Needle bar on the right                               | 213 999        | 540* | Cap screw M5x12             | 020 032 |




4.8.1 Continuation needle bed E14/12

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 2   | Locating wire $\varnothing 3,4$     | 213 995 | 503 | Cap screw M5x22      | 023 193 |
| 5   | Spring steel wire $\varnothing 0,6$ | 213 990 | 504 | Cap screw M5x12      | 022 943 |
| 6   | Spring steel wire $\varnothing 2,0$ | 213 996 | 506 | Springy thrust piece | 023 177 |
| 15  | Limiters on the left E10-14         | 205 764 | 509 | Shim0,05x18,5x34     | 023 196 |
| 16  | Limiters on the right E10-14        | 205 765 | 510 | Shim0,1x18,5x34      | 023 197 |
| 23  | Locating wire $\varnothing 2,8$     | 213 983 | 511 | Shim0,2x18,5x34      | 023 253 |
| 501 | Cap screw M5x8                      | 023 154 |     |                      |         |




## 4.9 Needle bed E6.2

| Pos      | Designation   | Id             | Pos  | Designation                         | Id      |
|----------|---|----------------|------|-------------------------------------|---------|
| $\Sigma$ | <b>Needle bed complete at the front + rear E6.2</b> | <b>263 877</b> | 19   | Cover rail at the rear              | 213 981 |
| 1        | Needle bed at the front + rear E12                  | 263 710        | 20   | Cover rail at the front E12         | 214 037 |
| 3        | Main trick wall E12                                 | 260 343        | 21   | Cover rail                          | 213 762 |
| 4        | Pressure slide E10-14                               | 213 919        | 22   | Cover rail                          | 213 763 |
| 7a       | Needle E6.2   | 207 349        | 28   | Bush                                | 206 090 |
| 7b       | Coupling part E10-12                                | 253 382        | 35   | Spring steel wire $\varnothing 2,0$ | 213 996 |
| 9a       | Intermediate slider with brake E10-12               | 255 535        | 36   | Stop screw                          | 235 244 |
| 10a      | Selection jack E10-12                               | 200 688        | 506  | Cap screw M5x8                      | 023 379 |
| 10b      | Selector spring E10-12                              | 200 691        | 507  | Cap screw M5x22                     | 023 193 |
| 11       | Holding-down jack bed at the rear E6.2              | 240 455        | 509  | Setscrew M3,5x2,3                   | 020 512 |
| 12       | Holding-down jack bed at the front E6.2             | 240 438        | 40*  | Disk brush                          | 235 612 |
| 13       | Knock-over bit E12                                  | 259 212        | 41*  | Container disk brush                | 233 012 |
| 14       | Holding-down jack (trick wall) E12                  | 259 213        | 42*  | Disk brush                          | 202 600 |
| 17       | Needle bar on the left                              | 213 998        | 43*  | Adjusting bolt                      | 251 772 |
| 18       | Needle bar on the right                             | 213 999        | 540* | Cap screw M5x12                     | 020 032 |




## 4.9.1 Continuation needle bed E6.2

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 2   | Locating wire $\varnothing 3,4$     | 213 995 | 507 | Cap screw M5x22      | 023 193 |
| 5   | Spring steel wire $\varnothing 0,6$ | 213 990 | 508 | Cap screw M5x12      | 022 943 |
| 15  | Limiters on the left                | 205 764 | 513 | Springy thrust piece | 023 177 |
| 16  | Limiters on the right               | 205 765 | 517 | Shim 0,05x18,5x34    | 023 196 |
| 26  | Locating wire $\varnothing 2,8$     | 213 983 | 518 | Shim 0,1x18,5x34     | 023 197 |
| 35  | Spring steel wire $\varnothing 2,0$ | 213 996 | 519 | Shim 0,2x18,5x34     | 023 253 |
| 505 | Cap screw M5x8                      | 023 154 |     |                      |         |




## 4.10 Needle bed E7.2

| Pos      | Designation   | Id             | Pos  | Designation             | Id      |
|----------|---|----------------|------|-------------------------|---------|
| <b>Σ</b> | <b>Needle bed complete at the front + rear E7.2</b> | <b>263 879</b> |      |                         |         |
| 1        | Needle bed at the front + rear E14                  | 263 711        | 18   | Cover rail              | 213 762 |
| 2        | Holding-down jack bed at the rear E7.2              | 240 456        | 19   | Cover rail              | 213 763 |
| 3        | Holding-down jack bed at the front E7.2             | 240 439        | 22   | Needle bar on the left  | 213 998 |
| 4        | Main trick wall E14                                 | 260 344        | 23   | Needle bar on the right | 213 999 |
| 5        | Pressure slide E10-14                               | 213 919        | 24   | Bush                    | 206 090 |
| 8        | Spring steel wire $\varnothing 2,0$                 | 213 996        | 27   | Stop screw              | 235 244 |
| 9a       | Needle E7.2 vosa special 112.70-62                  | 225 230        | 502  | Cap screw M5x8          | 023 379 |
| 9b       | Coupling part E14                                   | 253 383        | 503  | Cap screw M5x22         | 023 193 |
| 10a      | Intermediate slider with brake E14                  | 255 536        | 505  | Setscrew M3,5x3         | 020 512 |
| 11       | Selection jack with spring E14                      | 224 725        | 40*  | Disk brush              | 235 612 |
| 12       | Knock-over bit E14                                  | 209 649        | 41*  | Container disk brush    | 233 012 |
| 13       | Holding-down jack trick wall E7.2                   | 258 396        | 42*  | Disk brush              | 202 600 |
| 16       | Cover rail at the rear                              | 213 981        | 43*  | Adjusting bolt          | 251 772 |
| 17       | Cover rail at the front E14                         | 214 038        | 540* | Cap screw M5x12         | 020 032 |




4.10.1 Continuation needle bed E7.2

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 6   | Locating wire $\varnothing 3,4$     | 213 995 | 503 | Cap screw M5x22      | 023 193 |
| 7   | Spring steel wire $\varnothing 0,6$ | 213 990 | 504 | Cap screw M5x12      | 022 943 |
| 8   | Spring steel wire $\varnothing 2,0$ | 213 996 | 506 | Springy thrust piece | 023 177 |
| 14  | Limiters on the left E10-14         | 205 764 | 509 | Shim0,05x18,5x34     | 023 196 |
| 15  | Limiters on the right E10-14        | 205 765 | 510 | Shim0,1x18,5x34      | 023 197 |
| 20  | Locating wire $\varnothing 2,8$     | 213 983 | 511 | Shim0,2x18,5x34      | 023 253 |
| 501 | Cap screw M5x8                      | 023 154 |     |                      |         |




## 4.11 Needle bed E7.2 k&amp;w

| Pos      | Designation   | Id             | Pos  | Designation             | Id      |
|----------|---|----------------|------|-------------------------|---------|
| <b>Σ</b> | <b>Needle bed complete at the front + rear E7.2</b> | <b>263 881</b> |      |                         |         |
| 1        | Needle bed at the front + rear E14                  | 263 711        | 18   | Cover rail              | 213 762 |
| 2        | Holding-down jack bed at the rear E7.2              | 240 456        | 19   | Cover rail              | 213 763 |
| 3        | Holding-down jack bed at the front E7.2             | 240 439        | 22   | Needle bar on the left  | 213 998 |
| 4        | Main trick wall E14                                 | 260 344        | 23   | Needle bar on the right | 213 999 |
| 5        | Pressure slide E10-14                               | 213 919        | 24   | Bush                    | 206 090 |
| 8        | Spring steel wire $\varnothing 2,0$                 | 213 996        | 27   | Stop screw              | 235 244 |
| 9a       | Needle E7.2 vosa special 112.70-62                  | 225 230        | 502  | Cap screw M5x8          | 023 379 |
| 9b       | Coupling part E14                                   | 253 383        | 503  | Cap screw M5x22         | 023 193 |
| 10a      | Intermediate slider with brake E14                  | 255 536        | 505  | Setscrew M3,5x2,3       | 020 512 |
| 11       | Selection jack with spring E14                      | 224 725        | 40*  | Disk brush              | 235 612 |
| 12       | Knock-over bit E7.2                                 | 234 903        | 41*  | Container disk brush    | 233 012 |
| 13       | Holding-down jack E7.2                              | 236 954        | 42*  | Disk brush              | 202 600 |
| 16       | Cover rail at the rear                              | 213 981        | 43*  | Adjusting bolt          | 251 772 |
| 17       | Cover rail at the front E14                         | 272 171        | 540* | Cap screw M5x12         | 020 032 |




4.11.1 Continuation needle bed E7.2 k&w

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 6   | Locating wire $\varnothing 3,4$     | 213 995 | 503 | Cap screw M5x22      | 023 193 |
| 7   | Spring steel wire $\varnothing 0,6$ | 213 990 | 504 | Cap screw M5x12      | 022 943 |
| 8   | Spring steel wire $\varnothing 2,0$ | 213 996 | 506 | Springy thrust piece | 023 177 |
| 14  | Limiters on the left E10-14         | 205 764 | 509 | Shim0,05x18,5x34     | 023 196 |
| 15  | Limiters on the right E10-14        | 205 765 | 510 | Shim0,1x18,5x34      | 023 197 |
| 20  | Locating wire $\varnothing 2,8$     | 213 983 | 511 | Shim0,2x18,5x34      | 023 253 |
| 501 | Cap screw M5x8                      | 023 154 |     |                      |         |




## 4.12 Needle bed E8.2

| Pos      | Designation   | Id             | Pos  | Designation                                    | Id      |
|----------|---|----------------|------|--|---------|
| $\Sigma$ | <b>Needle bed complete at the front + rear E8.2</b> | <b>263 883</b> | 19   | Cover rail at the front E16                    | 222 531 |
| 1        | Needle bed at the front + rear E16                  | 263 712        | 20   | Cover rail                                     | 213 762 |
| 3        | Main trick wall E16                                 | 245 319        | 21   | Cover rail                                     | 213 763 |
| 4        | Pressure strip at the front E5-14                   | 219 536        | 24   | Bush   | 206 090 |
| 6a       | Needle E8.2   | 261 263        | 26   | Spring steel wire $\varnothing 2,0$            | 213 996 |
| 6b       | Coupling part E16-20                                | 253 384        | 27   | Pressure strip at the rear on the right E16-20 | 223 042 |
| 7        | Pressure strip at the rear E5-14                    | 219 537        | 28   | Stop screw                                     | 235 244 |
| 8        | Intermediate slider with brake E16-18               | 255 537        | 40*  | Disk brush                                     | 235 612 |
| 9        | Selection jack E16 with selector spring             | 222 265        | 41*  | Container disk brush                           | 233 012 |
| 10       | Holding-down jack bed at the rear E16               | 240 450        | 42*  | Disk brush                                     | 202 600 |
| 11       | Holding-down jack bed at the front E16              | 240 433        | 43*  | Adjusting bolt                                 | 251 772 |
| 12       | Knock-over bit wire position 0,8 mm E8.2            | 261 865        | 540* | Cap screw M5x12                                | 020 032 |
| 13       | Holding-down jack E16                               | 264 106        | 503  | Cap screw M6x14                                | 022 658 |
| 16       | Needle bar on the left                              | 213 998        | 506  | Cap screw M4-M5x8                              | 023 379 |
| 17       | Needle bar on the right                             | 213 999        | 507  | Cap screw M5x22                                | 023 193 |
| 18       | Cover rail at the rear                              | 213 981        | 509  | Setscrew M3,5x3-1                              | 020 512 |




## 4.12.1 Continuation needle bed E8.2

| Pos | Designation                         | Id      | Pos | Designation          | Id      |
|-----|-------------------------------------|---------|-----|----------------------|---------|
| 2   | Locating wire $\varnothing 3,4$     | 213 995 | 502 | Cap screw M5x22      | 023 193 |
| 5   | Spring steel wire $\varnothing 0,5$ | 220 759 | 503 | Cap screw M5x12-8.8  | 022 943 |
| 14  | Limiters on the left E16-20         | 220 821 | 505 | Springy thrust piece | 023 177 |
| 15  | Limiters on the right E16-20        | 220 822 | 508 | Shim0,05x18,5x34     | 023 196 |
| 22  | Locating wire $\varnothing 2,8$     | 223 922 | 509 | Shim0,1x18,5x34      | 023 197 |
| 26  | Spring steel wire $\varnothing 2,0$ | 213 996 | 510 | Shim0,2x18,5x34      | 023 253 |




## 4.13 Needle beds, fixing elements

| Pos      | Designation            | ID      | Pos | Designation | ID      |
|----------|------------------------|---------|-----|-------------|---------|
| $\Sigma$ | <b>Fixing elements</b> |         |     |             |         |
| 500      | Cap screw M8x25        | 020 142 | 501 | Washer      | 214 040 |




## 4.14 Right clamping and cutting bed E10 | E12 | E14 | E6.2 | E7.2

| Pos      | Designation                                  | Id      | Pos  | Designation                         | Id      |
|----------|--|---------|------|-------------------------------------|---------|
| $\Sigma$ | Clamping and cutting bed on the right E10-14 | 253 681 | 7    | Clamp on the right complete         | 244 602 |
| 1        | Guide plate EPT on the right E5-14           | 257 235 | 11   | Catch needle on the right E10-14    | 244 592 |
| 1a       | Guide plate on the right E5-14               | 257 231 | 12   | Intermediate part E10-14            | 244 591 |
| 1b       | Cover rail                                   | 243 923 | 13   | Coupling part E5-8                  | 253 381 |
| 1c       | Cover rail                                   | 243 924 | 14   | Intermediate slider with brake E5-8 | 255 534 |
| 1d       | Locating wire                                | 243 925 | 15   | Selection jack E4-8                 | 200 687 |
| 1e       | Axle   | 257 201 | 16   | Selector spring E4-8                | 200 690 |
| 1f       | Guide pin                                    | 211 351 | 17   | Holding strip on the right          | 256 995 |
| 1g       | Locating wire                                | 215 927 | 18   | Deflector plate on the right        | 255 555 |
| 1h       | Locating wire                                | 244 589 | 19   | Spring holder                       | 255 724 |
| 510      | Dowel pin 3x14                               | 252 771 | 20   | Threaded bolt                       | 255 723 |
| 511      | Setscrew M5x5                                | 236 061 | 500  | Cap screw M4x10                     | 023 136 |
| 2        | Cover on the right complete E5-14            | 260 966 | 501  | Hexagon nut M4                      | 023 046 |
| 2a       | Springy thrust piece N4                      | 260 235 | 502  | Washer 4                            | 020 870 |
| 3        | Catch hook on the right complete E5-14       | 260 968 | 503  | Pan-head screw M3x10                | 242 029 |
| 4        | Slider E5-14                                 | 258 050 | 505  | Compression spring 07x4,3x12,1      | 023 521 |
| 6        | Blade  | 243 948 | 570* | Cap screw M6x20                     | 244 824 |




## 4.15 Left clamping and cutting bed E10 | E12 | E14 | E6.2 | E7.2

| Pos      | Designation                          | Id             | Pos  | Designation                         | Id      |
|----------|--------------------------------------|----------------|------|-------------------------------------|---------|
| $\Sigma$ | Left clamping and cutting bed E10-14 | <b>253 682</b> | 7    | Clamp on the left complete          | 244 633 |
| 1        | Guide plate EPT on the left E5-14    | 257 236        | 11   | Catch needle on the left E5-14      | 244 630 |
| 1a       | Guide plate on the left E10-14       | 257 232        | 12   | Intermediate part E10-14            | 244 591 |
| 1b       | Cover rail                           | 243 923        | 13   | Coupling part E5-8                  | 253 381 |
| 1c       | Cover rail                           | 243 924        | 14   | Intermediate slider with brake E5-8 | 255 534 |
| 1d       | Locating wire                        | 243 925        | 15   | Selection jack E4-8                 | 200 687 |
| 1e       | Axle                                 | 257 201        | 16   | Selector spring E4-8                | 200 690 |
| 1f       | Guide pin                            | 211 351        | 17   | Holding strip on the left           | 256 996 |
| 1g       | Locating wire                        | 215 927        | 18   | Deflector plate on the left         | 255 556 |
| 1h       | Locating wire                        | 244 589        | 19   | Spring holder                       | 255 724 |
| 510      | Dowel pin 3x14                       | 252 771        | 20   | Threaded bolt                       | 255 723 |
| 511      | Setscrew M5x5                        | 236 061        | 500  | Cap screw M4x10                     | 023 136 |
| 2        | Cover on the left complete E5-14     | 260 967        | 501  | Hexagon nut M4                      | 023 046 |
| 2a       | Springy thrust piece N4              | 260 235        | 502  | Washer 4                            | 020 870 |
| 3        | Catch hook on the left E5-14         | 260 969        | 503  | Pan-head screw M3x10                | 242 029 |
| 4        | Slider E5-14                         | 258 050        | 505  | Compression spring 07x4,3x12,1      | 023 521 |
| 6        | Blade                                | 243 948        | 570* | Cap screw M6x20                     | 244 824 |




## 4.16 Right clamping and cutting bed E16|E18|E8.2

| Pos      | Designation                                  | Id      | Pos  | Designation                           | Id      |
|----------|--|---------|------|---------------------------------------|---------|
| $\Sigma$ | Clamping and cutting bed on the right E16-18 | 253 683 | 7    | Clamp on the right complete           | 244 602 |
| 1        | Guide plate EPT on the right E3              | 257 237 | 11   | Catch needle on the right E16-18      | 244 739 |
| 1a       | Guide plate on the right E3                  | 257 233 | 12   | Intermediate part                     | 244 741 |
| 1b       | Cover rail                                   | 243 923 | 13   | Coupling part E10-12                  | 253 382 |
| 1c       | Cover rail                                   | 243 924 | 14   | Intermediate slider with brake E10-12 | 255 535 |
| 1d       | Locating wire                                | 243 925 | 15   | Selection jack E10-12                 | 200 688 |
| 1e       | Axle   | 257 201 | 16   | Selector spring E10-12                | 200 691 |
| 1f       | Guide pin                                    | 211 351 | 17   | Holding strip on the right            | 256 995 |
| 1g       | Locating wire                                | 215 927 | 18   | Deflector plate on the right          | 255 555 |
| 1h       | Locating wire                                | 244 589 | 19   | Spring holder                         | 255 724 |
| 510      | Dowel pin 3x14                               | 252 771 | 20   | Threaded bolt                         | 255 723 |
| 511      | Setscrew M5x5                                | 236 061 | 500  | Cap screw M4x10                       | 023 136 |
| 2        | Cover on the right complete E16-18           | 259 406 | 501  | Hexagon nut M4                        | 023 046 |
| 2a       | Springy thrust piece N4                      | 260 235 | 502  | Washer 4                              | 020 870 |
| 3        | Catch hook on the right complete E16-18      | 259 310 | 503  | Pan-head screw M3x10                  | 242 029 |
| 4        | Slider E16-18                                | 259 309 | 505  | Compression spring 07x4,3x12,1        | 023 521 |
| 6        | Blade  | 243 948 | 570* | Cap screw M6x20                       | 244 824 |




## 4.17 Left clamping and cutting bed E16 | E18 | E8.2

| Pos      | Designation                          | Id                             | Pos  | Designation                           | Id      |
|----------|--------------------------------------|--------------------------------|------|---------------------------------------|---------|
| $\Sigma$ | Left clamping and cutting bed E16-18 | <b>253 684</b>                 | 7    | Clamp on the left complete            | 244 633 |
| 1        | Guide plate EPT on the left E16-18   | 257 238                        | 11   | Catch needle on the left E16-18       | 244 740 |
|          | 1a                                   | Guide plate on the left E16-18 | 12   | Intermediate part                     | 244 741 |
|          | 1b                                   | Cover rail                     | 13   | Coupling part E10-12                  | 253 382 |
|          | 1c                                   | Cover rail                     | 14   | Intermediate slider with brake E10-12 | 255 535 |
|          | 1d                                   | Locating wire                  | 15   | Selection jack E10-12                 | 200 688 |
|          | 1e                                   | Axle                           | 16   | Selector spring E10-12                | 200 691 |
|          | 1f                                   | Guide pin                      | 17   | Holding strip on the left             | 256 996 |
|          | 1g                                   | Locating wire                  | 18   | Deflector plate on the left           | 255 556 |
|          | 1h                                   | Locating wire                  | 19   | Spring holder                         | 255 724 |
|          | 510                                  | Dowel pin 3x14                 | 20   | Threaded bolt                         | 255 723 |
|          | 511                                  | Setscrew M5x5                  | 500  | Cap screw M4x10                       | 023 136 |
| 2        | Cover on the left complete E16-18    | 259 407                        | 501  | Hexagon nut M4                        | 023 046 |
| 2a       | Springy thrust piece N4              | 260 235                        | 502  | Washer 4                              | 020 870 |
| 3        | Catch hook on the left E16-18        | 259 311                        | 503  | Pan-head screw M3x10                  | 242 029 |
| 4        | Slider E16-18                        | 259 309                        | 505  | Compression spring 07x4,3x12,1        | 023 521 |
| 6        | Blade                                | 243 948                        | 570* | Cap screw M6x20                       | 244 824 |




# 5 Carriage




## 5.1 Carriage and linear guidance

| Pos | Designation                       | ID                              | Pos | Designation                      | ID      |
|-----|-----------------------------------|---------------------------------|-----|----------------------------------|---------|
| 1   | Front carriage complete E10       | 265 964                         | 2   | Rear carriage complete E10       | 265 965 |
|     | Front carriage complete E12       | 263 791                         |     | Rear carriage complete E12       | 263 792 |
|     | Front carriage complete E14       | 258 144                         |     | Rear carriage complete E14       | 258 145 |
|     | Front carriage complete E16   E18 | 263 793                         |     | Rear carriage complete E16   E18 | 263 794 |
|     | Front carriage complete E12m.10   | 265 966                         |     | Rear carriage complete E12m.10   | 265 967 |
|     | Front carriage complete E6.2      | 267 677                         |     | Rear carriage complete E6.2      | 267 678 |
|     | Front carriage complete E7.2      | 259 814                         |     | Rear carriage complete E7.2      | 259 815 |
|     | Front carriage complete E7.2 k&w  | 267 375                         |     | Rear carriage complete E7.2 k&w  | 267 376 |
|     | Front carriage complete E8.2      | 263 795                         |     | Rear carriage complete E8.2      | 263 796 |
|     | 3                                 | Cover strip for linear guidance |     | 262 985                          | 500     |
| 4   | Linear guidance LG = 2480         | 258 045                         | 501 | Cap screw M5x20                  | 258 909 |
| 5   | Linear guidance LG = 2280         | 258 044                         |     |                                  |         |




## 5.2 Carriage front and rear

| Pos | Designation                            | ID      | Pos                              | Designation   | ID  |                                  |
|-----|--|---------|----------------------------------|---|---|----------------------------------|
| 1   | Cam box complete E10                   | 265 741 | 2                                | Holding-down jack control complete E12-14   E12m.10 | 259 627   |                                  |
|     | Cam box complete E12                   | 265 742 |                                  | Holding-down jack control complete E16-18           | 259 628   |                                  |
|     | Cam box complete E14   E7.2(14/12)     | 265 743 |                                  | Holding-down jack control complete E12-14, E6.2     | 259 627   |                                  |
|     | Cam box complete E16   E18             | 265 744 |                                  | Holding-down jack control complete E7.2             | 259 629   |                                  |
|     | Cam box complete E6.2                  | 265 745 |                                  | Holding-down jack control complete E7.2 k&w         | 260 897   |                                  |
|     | Cam box complete E7.2                  | 265 746 |                                  | Holding-down jack control complete E8.2             | 259 630   |                                  |
|     | Cam box complete E7.2 k&w              | 263 377 |                                  | 3   | Front and rear carriage assembly 3 cam boxes complete | 258 146                          |
|     | Cam box complete E8.2                  | 265 747 |                                  |   | 5   | Selection system complete E10-12 |
|     | Cam box complete E12m.10               | 265 748 | Selection system complete E14    | 229 300   |   |                                  |
| 2   | Holding-down jack control complete E10 | 259 626 | Selection system complete E16-20 | 220 114   |   |                                  |




## 5.3 Carriage parts

| Pos      | Designation  | ID             | Pos | Designation                       | ID      |
|----------|--|----------------|-----|-----------------------------------|---------|
| <b>Σ</b> | <b>Front and rear carriage assembly 3 cam boxes complete</b> | <b>258 146</b> | 5   | Plate AFF carriage adjustment     | 257 977 |
| 1        | Carriage support   | 259 331        | 6   | Clamping plate                    | 257 959 |
| 2        | Carriage part complete                                       | 265 495        | 7   | Threaded insert M6x9              | 257 973 |
| 2.1      | Carriage part  | 265 494        | 9   | Adjusting eccentric AFDF carriage | 257 985 |
| 2.2      | Shim   | 225 312        | 14  | Bolt for carriage cover           | 259 668 |
| 2.3      | Shim   | 225 312        | 500 | Cap screw M8x30                   | 020 143 |
| 2.4      | Bushing  | 209 275        | 501 | Cap screw M6x16                   | 020 135 |
| 2.5      | Eccentric  | 222 983        | 503 | Washer 6                          | 020 872 |
| 2.6      | Locating bolt linking spot                                   | 244 179        | 505 | Threaded bush M12x8               | 259 705 |
| 520      | Threaded bush M12x11.5                                       | 041 863        | 506 | Washer 8                          | 020 873 |
| 521      | Pan-head screw M4x10   | 023 450        | 508 | Hexagon screw M6x25               | 257 917 |
| 522      | Fastening clip   | 008 323        | 509 | Cap screw M5x16                   | 022 726 |
| 524      | Circlip 6  | 021 022        | 511 | Washer 5                          | 020 871 |
| 4        | Shoulder screw   | 211 750        |     |                                   |         |




### 5.4 Continuation of carriage parts

| Pos | Designation                            | ID      | Pos | Designation                                | ID      |
|-----|--|---------|-----|--|---------|
| 1   | Front and rear carriage cover complete | 262 202 | 2   | Distributor 3 cam box                      | 265 523 |
| 1a  | Carriage cover ADF                     | 257 974 | 3   | Motor unit ATM complete                    | 251 827 |
| 1b  | Locating bolt ADF                      | 259 667 | 4   | Needle detector pre-assembled E10-18       | 256 475 |
| 510 | Washer 6,1x9x0,5                       | 023 554 | 5   | Sinker opener complete                     | 256 623 |
| 511 | Hexagon nut M6                         | 022 899 | 6   | Brush holder complete E5-8                 | 265 553 |
| 512 | Serrated lock washer J 6,4             | 022 385 |     | Brush holder complete E10-14   E6.2   E7.2 | 265 552 |
| 514 | O-ring 3x2                             | 242 420 |     | Brush holder complete E16   E18   E8.2     | 272 307 |
| 515 | Compression spring<br>0,48x7,02x17,29  | 023 654 | 501 | Cap screw M4x35                            | 023 550 |
|     |  |         | 513 | Cap screw M4x20                            | 023 171 |




## 5.5 Brush holder

| Pos      | Designation                        | ID             | Pos | Designation                        | ID      |
|----------|------------------------------------|----------------|-----|------------------------------------|---------|
| <b>Σ</b> | <b>Brush holder complete</b>       |                | 4   | Brush                              |         |
|          | E16   E18   E18m.16   E8.2         | <b>265 553</b> |     | E16   E18   E18m.16   E8.2         | 268 924 |
|          | E10   E12   E14   E14/12   E12m.10 | <b>265 552</b> |     | E10   E12   E14   E14/12   E12m.10 | 268 930 |
|          | E6.2   E7.2   E7.2 kw              |                |     | E6.2   E7.2   E7.2 kw              |         |
| 1        | Brush holder                       | 213 009        | 500 | Countersunk head screw M4x12       | 023 062 |
| 2        | Brush clamp                        | 265 439        | 501 | Hexagon nut                        | 020 856 |
| 3        | Threaded rod                       | 209 740        | 502 | Shim ring 5x10x0,5                 | 023 348 |
|          |                                    |                | 503 | Retaining ring 5x0,6               | 023 347 |




### 5.6 Needle detector

| Pos      | Designation                          | ID      | Pos | Designation  | ID      |
|----------|--------------------------------------|---------|-----|--|---------|
| <b>Σ</b> | <b>Needle detector</b>               |         | 504 | Compression spring 0,4x4x11,2                      | 256 952 |
| 1        | Needle detector pre-assembled E10-18 | 256 475 | 505 | Circlip  | 021 018 |
| 11       | Cable of needle detector complete    | 261 856 | 506 | Circlip  | 023 565 |
| 12       | Retainer                             | 256 476 | 507 | Cable tape 92x2,4                                  | 008 378 |
| 13       | Switch rocker                        | 256 477 | 2   | Sensor pre-assembled E10   E12   E14   E7.2   E6.2 | 256 454 |
| 14       | Set-out plate                        | 256 094 | 21  | Sensor E10-14                                      | 255 758 |
| 15       | Bolts                                | 256 492 | 22  | Angle  | 255 757 |
| 16       | Stop bolt                            | 256 493 | 520 | Pan head screw M4x6                                | 023 427 |
| 500      | Pan head screw M5x10                 | 023 247 | 2   | Sensor pre-assembled E16   E18   E8.2              | 256 784 |
| 501      | Pan head screw M2x8                  | 258 310 | 21  | Sensor E16-18                                      | 255 759 |
| 502      | Dowel pin4x10-A-St                   | 023 753 | 22  | Angle  | 255 757 |
| 503      | Compression spring 4,3x0,45x10       | 021 398 | 520 | Pan head screw M4x6                                | 023 427 |




### 5.7 Holding-down jack control

| Pos      | Designation                               | Id             | Pos | Designation                            | Id      |
|----------|---|----------------|-----|--|---------|
| <b>Σ</b> | <b>Holding-down jack control complete</b> |                |     |  |         |
|          | E10                                       | <b>259 626</b> | 22  | E7.2                                   | 256 394 |
|          | E12   E14   E6.2                          | <b>259 627</b> |     | E7.2 k&w                               | 260 895 |
|          | E16   E18                                 | <b>259 628</b> |     | E8.2                                   | 256 395 |
|          | E7.2                                      | <b>259 629</b> | 23  | Slider on the left complete            |         |
|          | E7.2 k&w                                  | <b>260 897</b> |     | E10                                    | 256 396 |
|          | E8.2                                      | <b>259 630</b> |     | E12   E14   E6.2                       | 256 397 |
| 1        | Assembly plate complete                   | 256 311        |     | E16   E18                              | 256 398 |
| 4        | Adjusting plate                           | 256 388        |     | E7.2                                   | 256 399 |
| 5        | Plunger                                   | 256 059        |     | E7.2 k&w                               | 260 894 |
| 11       | Slider on the right                       | 259 457        |     | E8.2                                   | 256 400 |
| 12       | Slider on the left                        | 259 456        | 24  | Bolts                                  | 209 722 |
| 21       | Base plate                                | 259 170        | 500 | Pan head screw M4x6                    | 023 427 |
| 22       | Slider on the right complete              |                | 501 | Cap screw M4x12                        | 241 859 |
|          | E10                                       | 256 391        | 506 | Cap screw M4x8                         | 022 501 |
|          | E12   E14   E6.2                          | 256 392        | 520 | Shim ring 5x8x0.5                      | 256 371 |
|          | E16   E18                                 | 256 393        | 521 | Retaining ring 5x0,6                   | 023 347 |
|          |   |                | 30* | Eccentric of holding-down jack control | 256 994 |




## 5.8 Grease supply

| Pos      | Designation                           | ID      | Pos | Designation           | ID      |
|----------|---------------------------------------|---------|-----|-----------------------|---------|
| <b>Σ</b> | <b>Grease supply</b>                  |         |     |                       |         |
| 1        | Hydraulic-type lubricating nipple AM6 | 021 813 | 4   | Swivelling connection | 240 789 |
| 2        | Adaptor                               | 265 493 | 5   | Tubular D4, 200 mm    | 240 788 |
| 3        | Straight plug connectors D4           | 235 051 | 6   | Tubular D4, 90 mm     | 265 403 |




## 5.9 Cam box E10

| Pos      | Designation                               | Id             | Pos | Designation                   | Id      |
|----------|---|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Cam box complete E10</b>               | <b>265 741</b> |     |                               |         |
| 1        | Cam plate 3 cam boxes E10-18              | 264 747        | 37  | d Circlip                     | 023 565 |
| 22       | Stay bolt                                 | 254 839        |     | e Disk                        | 259 647 |
| 23       | Guide of pressure part complete           | 253 480        |     | f Washer                      | 022 893 |
| 34       | Loop sinking cam on the left completeE10  | 254 246        | 38  | Slider pressure part complete | 251 834 |
| 35       | Loop sinking cam on the right completeE10 | 254 247        | 43  | Holding piece                 | 251 828 |
| 36       | Rod guide on the left complete            | 252 662        | 503 | Cap screw M3x6                | 022 589 |
| 37       | Rod guide on the right complete           | 252 663        | 505 | Shim0,5x12x75                 | 236 654 |
| a        | Rod guide part                            | 258 148        | 509 | Pan-head screw M3x4           | 023 142 |
| b        | Spring rod                                | 252 661        | 511 | Shim0,03x8x28                 | 023 452 |
| c        | Compression spring                        | 257 082        | 512 | Shim0,05x8x28                 | 023 020 |




## 5.9.1 Cams E10

| Pos | Designation                                | Id      | Pos | Designation   | Id      |
|-----|--|---------|-----|---|---------|
| 2   | Entry cam on the left at the top E10-18    | 266 549 | 24  | Tuck pressure cam                                       | 253 828 |
| 3   | Entry cam on the right at the top E10-18   | 266 590 | 25  | Limiting cam E10   E7.2                                 | 251 993 |
| 4   | Entry cam at the top E10-18                | 265 660 | 26  | Pointer E10   | 251 994 |
| 5   | Knitting position cam E10-14   E6.2   E7.2 | 255 021 | 27  | Screw   | 210 335 |
| 6   | Plate on the left E10-18                   | 255 389 | 28  | Stitch cam on the left E10-14   E7.2                    | 254 331 |
| 7   | Plate on the right E10-18                  | 255 390 | 29  | Stitch cam on the right E10-14   E7.2                   | 254 332 |
| 8   | Entry cam on the left E10-18               | 255 391 | 30  | Tuck limiting cam E10   E7.2                            | 254 295 |
| 9   | Entry cam on the right E10-18              | 255 392 | 31  | Raising cam plate E10-18                                | 251 992 |
| 10  | Pressure strip E10-14                      | 255 540 | 32  | Receiving cam E10   E12                                 | 251 997 |
| 11  | Cam guide at the top E10-18                | 258 161 | 33  | Raising cam without split-stitch E10   E12              | 254 334 |
| 12  | Cam guide E10-18                           | 264 188 |     | Raising cam with split-stitch E10   E12                 | 254 335 |
| 13  | Cam on the left E10-18                     | 255 613 | 39  | Cam at the right E10-18                                 | 259 769 |
| 14  | Cam at the right E10-18                    | 255 614 | 40  | Knitting position cam on the left E10-14   E6.2   E7.2  | 255 022 |
| 15  | Limiting cam on the left                   | 264 051 | 41  | Knitting position cam on the right E10-14   E6.2   E7.2 | 255 023 |
| 16  | Limiting cam on the right                  | 264 052 | 49  | Limiting cam middle                                     | 264 053 |
| 17  | Cam on the left E10-18                     | 259 768 | 50  | Delivery pressure cam                                   | 253 838 |
| 18  | Cam E10-18                                 | 258 152 | 51  | Offering cam  | 210 185 |
| 19  | Selection cam on the left E10-18           | 251 876 | 500 | Cap screw M4x8  | 020 091 |
| 20  | Selection cam on the right E10-18          | 251 877 | 510 | Cap screw M3x8  | 020 081 |
| 21  | Selection cam E10-18                       | 251 875 |     |   |         |




## 5.10 Cam box E12

| Pos      | Designation                                  | Id             | Pos | Designation                   | Id      |
|----------|--|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Cam box complete E12</b>                  | <b>265 742</b> | 37  | d Circlip                     | 023 565 |
| 1        | Cam plate E10-18                             | 264 747        |     | e Disk                        | 259 647 |
| 22       | Stay bolt                                    | 254 839        |     | f Washer                      | 022 893 |
| 23       | Guide of pressure part complete              | 253 480        | 38  | Slider pressure part complete | 251 834 |
| 34       | Loop sinking cam on the left completeE12-14  | 254 248        | 43  | Holding piece                 | 251 828 |
| 35       | Loop sinking cam on the right completeE12-14 | 254 249        | 503 | Cap screw M3x6                | 022 589 |
| 36       | Rod guide on the left complete               | 252 662        | 505 | Shim0,5x12x75                 | 236 654 |
| 37       | Rod guide on the right complete              | 252 663        | 509 | Pan-head screw M3x4           | 023 142 |
| a        | Rod guide part                               | 258 148        | 511 | Shim0,03x8x28                 | 023 452 |
| b        | Spring rod                                   | 252 661        | 512 | Shim0,05x8x28                 | 023 020 |
| c        | Compression spring                           | 257 082        |     |                               |         |




## 5.10.1 Cams E12

| Pos | Designation                                | Id      | Pos | Designation   | Id      |
|-----|--|---------|-----|---|---------|
| 2   | Entry cam on the left at the top E10-18    | 266 549 | 24  | Tuck pressure cam                                       | 253 828 |
| 3   | Entry cam on the right at the top E10-18   | 266 590 | 25  | Limiting cam E12-14                                     | 252 522 |
| 4   | Entry cam at the top E10-18                | 265 660 | 26  | Pointer E10   | 251 994 |
| 5   | Knitting position cam E10-14   E6.2   E7.2 | 255 021 | 27  | Screw   | 210 335 |
| 6   | Plate on the left E10-18                   | 255 389 | 28  | Stitch cam on the left E10-14   E7.2                    | 254 331 |
| 7   | Plate on the right E10-18                  | 255 390 | 29  | Stitch cam on the right E10-14   E7.2                   | 254 332 |
| 8   | Entry cam on the left E10-18               | 255 391 | 30  | Tuck limiting cam E12-14                                | 254 298 |
| 9   | Entry cam on the right E10-18              | 255 392 | 31  | Raising cam plate E10-18                                | 251 992 |
| 10  | Pressure strip E10-14                      | 255 540 | 32  | Receiving cam E10   E12                                 | 251 997 |
| 11  | Cam guide at the top E10-18                | 258 161 | 33  | Raising cam without split-stitch E10   E12              | 254 334 |
| 12  | Cam guide E10-18                           | 264 188 |     | Raising cam with split-stitch E10   E12                 | 254 335 |
| 13  | Cam on the left E10-18                     | 255 613 | 39  | Cam at the right E10-18                                 | 259 769 |
| 14  | Cam at the right E10-18                    | 255 614 | 40  | Knitting position cam on the left E10-14   E6.2   E7.2  | 255 022 |
| 15  | Limiting cam on the left                   | 264 051 | 41  | Knitting position cam on the right E10-14   E6.2   E7.2 | 255 023 |
| 16  | Limiting cam on the right                  | 264 052 | 49  | Limiting cam middle                                     | 264 053 |
| 17  | Cam on the left E10-18                     | 259 768 | 50  | Delivery pressure cam                                   | 253 838 |
| 18  | Cam E10-18                                 | 258 152 | 51  | Offering cam  | 210 185 |
| 19  | Selection cam on the left E10-18           | 251 876 | 500 | Cap screw M4x8  | 020 091 |
| 20  | Selection cam on the right E10-18          | 251 877 | 510 | Cap screw M3x8  | 020 081 |
| 21  | Selection cam E10-18                       | 251 875 |     |   |         |




## 5.11 Cam box E14 | E14/12

| Pos      | Designation                                   | Id             | Pos | Designation                   | Id      |
|----------|---|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Cam box complete E14</b>                   | <b>265 743</b> |     |                               |         |
| 1        | Cam plate E10-18                              | 264 747        | 37  | d Circlip                     | 023 565 |
| 22       | Stay bolt                                     | 254 839        |     | e Disk                        | 259 647 |
| 23       | Guide of pressure part complete               | 253 480        |     | f Washer                      | 022 893 |
| 34       | Loop sinking cam on the left complete E12-14  | 254 248        | 38  | Slider pressure part complete | 251 834 |
| 35       | Loop sinking cam on the right complete E12-14 | 254 249        | 43  | Holding piece                 | 251 828 |
| 36       | Rod guide on the left complete                | 252 662        | 503 | Cap screw M3x6                | 022 589 |
| 37       | Rod guide on the right complete               | 252 663        | 505 | Shim0,5x12x75                 | 236 654 |
| a        | Rod guide part                                | 258 148        | 509 | Pan-head screw M3x4           | 023 142 |
| b        | Spring rod                                    | 252 661        | 511 | Shim0,03x8x28                 | 023 452 |
| c        | Compression spring                            | 257 082        | 512 | Shim0,05x8x28                 | 023 020 |




5.11.1 Cams E14 | E14/12

| Pos | Designation                                | Id      | Pos | Designation   | Id      |
|-----|--|---------|-----|---|---------|
| 2   | Entry cam on the left at the top E10-18    | 266 549 | 24  | Tuck pressure cam                                       | 253 828 |
| 3   | Entry cam on the right at the top E10-18   | 266 590 | 25  | Limiting cam E12-14                                     | 252 522 |
| 4   | Entry cam at the top E10-18                | 265 660 | 26  | Pointer E10   | 251 994 |
| 5   | Knitting position cam E10-14   E6.2   E7.2 | 255 021 | 27  | Screw   | 210 335 |
| 6   | Plate on the left E10-18                   | 255 389 | 28  | Stitch cam on the left E10-14   E7.2                    | 254 331 |
| 7   | Plate on the right E10-18                  | 255 390 | 29  | Stitch cam on the right E10-14   E7.2                   | 254 332 |
| 8   | Entry cam on the left E10-18               | 255 391 | 30  | Tuck limiting cam E12   E14                             | 254 298 |
| 9   | Entry cam on the right E10-18              | 255 392 | 31  | Raising cam plate E10-18                                | 251 992 |
| 10  | Pressure strip E10-14                      | 255 540 | 32  | Receiving cam E14                                       | 252 607 |
| 11  | Cam guide at the top E10-18                | 258 161 | 33  | Raising cam without split-stitch E14                    | 254 336 |
| 12  | Cam guide E10-18                           | 264 188 |     | Raising cam with split-stitch E14                       | 254 337 |
| 13  | Cam on the left E10-18                     | 255 613 | 39  | Cam at the right E10-18                                 | 259 769 |
| 14  | Cam at the right E10-18                    | 255 614 | 40  | Knitting position cam on the left E10-14   E6.2   E7.2  | 255 022 |
| 15  | Limiting cam on the left                   | 264 051 | 41  | Knitting position cam on the right E10-14   E6.2   E7.2 | 255 023 |
| 16  | Limiting cam on the right                  | 264 052 | 49  | Limiting cam middle                                     | 264 053 |
| 17  | Cam on the left E10-18                     | 259 768 | 50  | Delivery pressure cam                                   | 253 838 |
| 18  | Cam E10-18                                 | 258 152 | 51  | Offering cam  | 210 185 |
| 19  | Selection cam on the left E10-18           | 251 876 | 500 | Cap screw M4x8  | 020 091 |
| 20  | Selection cam on the right E10-18          | 251 877 | 510 | Cap screw M3x8  | 020 081 |
| 21  | Selection cam E10-18                       | 251 875 |     |   |         |




## 5.12 Cam box E16 | E18 | E18m.16

| Pos      | Designation                                   | Id             | Pos | Designation                   | Id      |
|----------|---|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Cam box complete E16-18</b>                | <b>265 744</b> |     |                               |         |
| 1        | Cam plate E10-18                              | 264 747        | 37  | d Circlip                     | 023 565 |
| 22       | Stay bolt                                     | 254 839        |     | e Disk                        | 259 647 |
| 23       | Guide of pressure part complete               | 253 480        |     | f Washer                      | 022 893 |
| 34       | Loop sinking cam on the left complete E16-18  | 251 965        | 38  | Slider pressure part complete | 251 834 |
| 35       | Loop sinking cam on the right complete E16-18 | 251 966        | 43  | Holding piece                 | 251 828 |
| 36       | Rod guide on the left complete                | 252 662        | 503 | Cap screw M3x6                | 022 589 |
| 37       | Rod guide on the right complete               | 252 663        | 505 | Shim0,5x12x75                 | 236 654 |
| a        | Rod guide part                                | 258 148        | 509 | Pan-head screw M3x4           | 023 142 |
| b        | Spring rod                                    | 252 661        | 511 | Shim0,03x8x28                 | 023 452 |
| c        | Compression spring                            | 257 082        | 512 | Shim0,05x8x28                 | 023 020 |




## 5.12.1 Cams E16 | E18 | E18m.16

| Pos | Designation                              | Id      | Pos | Designation                                      | Id      |
|-----|--|---------|-----|--|---------|
| 2   | Entry cam on the left at the top E10-18  | 266 549 | 24  | Tuck pressure cam                                | 253 828 |
| 3   | Entry cam on the right at the top E10-18 | 266 590 | 25  | Limiting cam E16-18                              | 252 646 |
| 4   | Entry cam at the top E10-18              | 265 660 | 26  | Pointer E16-18                                   | 252 656 |
| 5   | Knitting position cam E16-18   E8.2      | 255 027 | 27  | Screw  | 210 335 |
| 6   | Plate on the left E10-18                 | 255 389 | 28  | Stitch cam on the left E16-18   E8.2             | 254 338 |
| 7   | Plate on the right E10-18                | 255 390 | 29  | Stitch cam on the right E16-18   E8.2            | 254 339 |
| 8   | Entry cam on the left E10-18             | 255 391 | 30  | Tuck limiting cam E16-18                         | 254 299 |
| 9   | Entry cam on the right E10-18            | 255 392 | 31  | Raising cam plate E10-18                         | 251 992 |
| 10  | Pressure strip E16-18                    | 256 681 | 32  | Receiving cam E16-18                             | 252 654 |
| 11  | Cam guide at the top E10-18              | 258 161 | 33  | Raising cam without split-stitch E16-18          | 254 340 |
| 12  | Cam guide E10-18                         | 264 188 |     | Raising cam with split-stitch E16-18             | 254 341 |
| 13  | Cam on the left E10-18                   | 255 613 | 39  | Cam at the right E10-18                          | 259 769 |
| 14  | Cam at the right E10-18                  | 255 614 | 40  | Knitting position cam on the left E16-18   E8.2  | 255 028 |
| 15  | Limiting cam on the left                 | 264 051 | 41  | Knitting position cam on the right E16-18   E8.2 | 255 029 |
| 16  | Limiting cam on the right                | 264 052 | 49  | Limiting cam middle                              | 264 053 |
| 17  | Cam on the left E10-18                   | 259 768 | 50  | Delivery pressure cam                            | 253 838 |
| 18  | Cam E10-18                               | 258 152 | 51  | Offering cam                                     | 210 185 |
| 19  | Selection cam on the left E10-18         | 251 876 | 500 | Cap screw M4x8                                   | 020 091 |
| 20  | Selection cam on the right E10-18        | 251 877 | 510 | Cap screw M3x8                                   | 020 081 |
| 21  | Selection cam E10-18                     | 251 875 |     |  |         |




## 5.13 Cam box E12m.10

| Pos      | Designation                                  | Id             | Pos | Designation                   | Id      |
|----------|--|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Cam box complete E12m.10</b>              | <b>265 748</b> |     |                               |         |
| 1        | Cam plate E10-18                             | 264 747        | 37  | d Circlip                     | 023 565 |
| 22       | Stay bolt                                    | 254 839        |     | e Disk                        | 259 647 |
| 23       | Guide of pressure part complete              | 253 480        |     | f Washer                      | 022 893 |
| 34       | Loop sinking cam on the left completeE12-14  | 254 248        | 38  | Slider pressure part complete | 251 834 |
| 35       | Loop sinking cam on the right completeE12-14 | 254 249        | 43  | Holding piece                 | 251 828 |
| 36       | Rod guide on the left complete               | 252 662        | 503 | Cap screw M3x6                | 022 589 |
| 37       | Rod guide on the right complete              | 252 663        | 505 | Shim0,5x12x75                 | 236 654 |
| a        | Rod guide part                               | 258 148        | 509 | Pan-head screw M3x4           | 023 142 |
| b        | Spring rod                                   | 252 661        | 511 | Shim0,03x8x28                 | 023 452 |
| c        | Compression spring                           | 257 082        | 512 | Shim0,05x8x28                 | 023 020 |




5.13.1 Cams E12m.10

| Pos | Designation                                | Id      | Pos | Designation   | Id      |
|-----|--|---------|-----|---|---------|
| 2   | Entry cam on the left at the top E10-18    | 266 549 | 24  | Tuck pressure cam                                       | 253 828 |
| 3   | Entry cam on the right at the top E10-18   | 266 590 | 25  | Limiting cam E10   E7.2                                 | 251 993 |
| 4   | Entry cam at the top E10-18                | 265 660 | 26  | Pointer E10   | 251 994 |
| 5   | Knitting position cam E10-14   E6.2   E7.2 | 255 021 | 27  | Screw   | 210 335 |
| 6   | Plate on the left E10-18                   | 255 389 | 28  | Stitch cam on the left E10-14   E7.2                    | 254 331 |
| 7   | Plate on the right E10-18                  | 255 390 | 29  | Stitch cam on the right E10-14   E7.2                   | 254 332 |
| 8   | Entry cam on the left E10-18               | 255 391 | 30  | Tuck limiting cam E10   E7.2                            | 254 295 |
| 9   | Entry cam on the right E10-18              | 255 392 | 31  | Raising cam plate E10-18                                | 251 992 |
| 10  | Pressure strip E10-14                      | 255 540 | 32  | Receiving cam E10-12                                    | 251 997 |
| 11  | Cam guide at the top E10-18                | 258 161 | 33  | Raising cam without split-stitch E10-12                 | 254 334 |
| 12  | Cam guide E10-18                           | 264 188 |     | Raising cam with split-stitch E10-12                    | 254 335 |
| 13  | Cam E10-18                                 | 255 613 | 39  | Cam at the right E10-18                                 | 259 769 |
| 14  | Cam at the right E10-18                    | 255 614 | 40  | Knitting position cam on the left E10-14   E6.2   E7.2  | 255 022 |
| 15  | Limiting cam on the left                   | 264 051 | 41  | Knitting position cam on the right E10-14   E6.2   E7.2 | 255 023 |
| 16  | Limiting cam on the right                  | 264 052 | 49  | Limiting cam middle                                     | 264 053 |
| 17  | Cam on the left E10-18                     | 259 768 | 50  | Delivery pressure cam                                   | 253 838 |
| 18  | Cam E10-18                                 | 258 152 | 51  | Offering cam  | 210 185 |
| 19  | Selection cam on the left E10-18           | 251 876 | 500 | Cap screw M4x8  | 020 091 |
| 20  | Selection cam on the right E10-18          | 251 877 | 510 | Cap screw M3x8  | 020 081 |
| 21  | Selection cam E10-18                       | 251 875 |     |   |         |




## 5.14 Cam box E6.2

| Pos      | Designation                                  | Id             | Pos | Designation                  | Id      |
|----------|--|----------------|-----|------------------------------|---------|
| <b>Σ</b> | <b>Cam box complete E6.2</b>                 | <b>265 212</b> | 37  | d Circlip                    | 023 565 |
| 1        | Cam plate 3 cam boxes E10-18                 | 264 747        |     | e Disk                       | 259 647 |
| 22       | Stay bolt                                    | 254 839        |     | f Washer                     | 022 893 |
| 23       | Guide of pressure cam complete               | 253 480        | 38  | Slider pressure cam complete | 251 834 |
| 34       | Loop sinking cam on the left completeE12-14  | 254 248        | 43  | Holding piece                | 251 828 |
| 35       | Loop sinking cam on the right completeE12-14 | 254 249        | 503 | Cap screw M3x6               | 022 589 |
| 36       | Rod guide on the left complete               | 252 662        | 505 | Shim 0,5x12x75               | 236 654 |
| 37       | Rod guide on the right complete              | 252 663        | 509 | Pan head screw M3x4          | 023 142 |
| a        | Rod guide part                               | 258 148        | 511 | Shim 0,03x8x28               | 023 452 |
| b        | Spring rod                                   | 252 661        | 512 | Shim 0,05x8x28               | 023 020 |
| c        | Compression spring                           | 257 082        |     |                              |         |




5.14.1 Cams E6.2

| Pos | Designation                                | Id      | Pos | Designation   | Id      |
|-----|--|---------|-----|---|---------|
| 2   | Entry cam on the left at the top E10-18    | 256 690 | 24  | Tuck pressure cam                                       | 253 828 |
| 3   | Entry cam on the right at the top E10-18   | 256 691 | 25  | Limiting cam E6.2                                       | 252 955 |
| 4   | Entry cam at the top E10-18                | 256 689 | 26  | Pointer E10   | 251 994 |
| 5   | Knitting position cam E10-14   E6.2   E7.2 | 255 021 | 27  | Screw   | 210 335 |
| 6   | Plate on the left E10-18                   | 255 389 | 28  | Stitch cam on the left E6.2                             | 254 342 |
| 7   | Plate on the right E10-18                  | 255 390 | 29  | Stitch cam on the right E6.2                            | 254 343 |
| 8   | Entry cam on the left E10-18               | 255 391 | 30  | Tuck limiting cam E6.2                                  | 254 301 |
| 9   | Entry cam on the right E10-18              | 255 392 | 31  | Raising cam plate E10-18                                | 251 992 |
| 10  | Pressure strip E10-14                      | 255 540 | 32  | Receiving cam E6.2                                      | 252 960 |
| 11  | Cam guide at the top E10-18                | 258 161 | 33  | Raising cam without split-stitch E6.2                   | 254 344 |
| 12  | Cam guide E10-18                           | 255 541 |     | Raising cam with split-stitch E6.2                      | 254 345 |
| 13  | Cam on the left E10-18                     | 255 613 | 39  | Cam at the right E10-E18                                | 259 769 |
| 14  | Cam at the right E10-18                    | 255 614 | 40  | Knitting position cam on the left E10-14   E6.2   E7.2  | 255 022 |
| 15  | Limiting cam on the left                   | 264 051 | 41  | Knitting position cam on the right E10-14   E6.2   E7.2 | 255 023 |
| 16  | Limiting cam on the right                  | 264 052 | 49  | Limiting cam middle                                     | 264 053 |
| 17  | Cam on the left E10-18                     | 259 768 | 50  | Delivery pressure cam                                   | 253 838 |
| 18  | Cam E10-18                                 | 258 152 | 51  | Offering cam  | 210 185 |
| 19  | Selection cam on the left E10-18           | 251 876 | 500 | Cap screw M4x8  | 020 091 |
| 20  | Selection cam on the right E10-18          | 251 877 | 510 | Cap screw M3x8  | 020 081 |
| 21  | Selection cam E10-18                       | 251 875 |     |   |         |




## 5.15 Cam box E7.2

| Pos      | Designation                                  | Id             | Pos | Designation                   | Id      |
|----------|--|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Cam box complete E7.2</b>                 | <b>265 746</b> |     |                               |         |
| 1        | Cam plate E10-18                             | 264 747        | 37  | d Circlip                     | 023 565 |
| 22       | Stay bolt                                    | 254 839        |     | e Disk                        | 259 647 |
| 23       | Guide of pressure part complete              | 253 480        |     | f Washer                      | 022 893 |
| 34       | Loop sinking cam on the left completeE12-14  | 254 248        | 38  | Slider pressure part complete | 251 834 |
| 35       | Loop sinking cam on the right completeE12-14 | 254 249        | 43  | Holding piece                 | 251 828 |
| 36       | Rod guide on the left complete               | 252 662        | 503 | Cap screw M3x6                | 022 589 |
| 37       | Rod guide on the right complete              | 252 663        | 505 | Shim0,5x12x75                 | 236 654 |
| a        | Rod guide part                               | 258 148        | 509 | Pan-head screw M3x4           | 023 142 |
| b        | Spring rod                                   | 252 661        | 511 | Shim0,03x8x28                 | 023 452 |
| c        | Compression spring                           | 257 082        | 512 | Shim0,05x8x28                 | 023 020 |




5.15.1 Cams E7.2

| Pos | Designation                                | Id      | Pos | Designation   | Id      |
|-----|--|---------|-----|---|---------|
| 2   | Entry cam on the left at the top E10-18    | 266 549 | 24  | Tuck pressure cam                                       | 253 828 |
| 3   | Entry cam on the right at the top E10-18   | 266 590 | 25  | Limiting cam E10   E7.2                                 | 251 993 |
| 4   | Entry cam at the top E10-18                | 265 660 | 26  | Pointer E10   | 251 994 |
| 5   | Knitting position cam E10-14   E6.2   E7.2 | 255 021 | 27  | Screw   | 210 335 |
| 6   | Plate on the left E10-18                   | 255 389 | 28  | Stitch cam on the left E10-14   E7.2                    | 254 331 |
| 7   | Plate on the right E10-18                  | 255 390 | 29  | Stitch cam on the right E10-14   E7.2                   | 254 332 |
| 8   | Entry cam on the left E10-18               | 255 391 | 30  | Tuck limiting cam E10   E7.2                            | 254 295 |
| 9   | Entry cam on the right E10-18              | 255 392 | 31  | Raising cam plate E10-18                                | 251 992 |
| 10  | Pressure strip E10-14                      | 255 540 | 32  | Receiving cam E10-12                                    | 251 997 |
| 11  | Cam guide E10-18                           | 258 161 | 33  | Raising cam without split-stitch E10-12                 | 254 334 |
| 12  | Cam guide E10-18                           | 264 188 |     | Raising cam with split-stitch E10-12                    | 254 335 |
| 13  | Cam on the left E10-18                     | 255 613 | 39  | Cam at the right E10-18                                 | 259 769 |
| 14  | Cam at the right E10-18                    | 255 614 | 40  | Knitting position cam on the left E10-14   E6.2   E7.2  | 255 022 |
| 15  | Limiting cam on the left                   | 264 051 | 41  | Knitting position cam on the right E10-14   E6.2   E7.2 | 255 023 |
| 16  | Limiting cam on the right                  | 264 052 | 49  | Limiting cam middle                                     | 264 053 |
| 17  | Cam on the left E10-18                     | 259 768 | 50  | Delivery pressure cam                                   | 253 838 |
| 18  | Cam E10-18                                 | 258 152 | 51  | Offering cam  | 210 185 |
| 19  | Selection cam on the left E10-18           | 251 876 | 500 | Cap screw M4x8  | 020 091 |
| 20  | Selection cam on the right E10-18          | 251 877 | 510 | Cap screw M3x8  | 020 081 |
| 21  | Selection cam E10-18                       | 251 875 |     |   |         |




## 5.16 Cam box E7.2 k&amp;w

| Pos      | Designation                                   | ID             | Pos | Designation                  | ID      |
|----------|---|----------------|-----|------------------------------|---------|
| <b>Σ</b> | <b>Cam box complete E7.2 k&amp;w</b>          | <b>267 377</b> |     |                              |         |
| 1        | Cam plate E10-18                              | 264 747        | 37  | d Circlip                    | 023 565 |
| 22       | Stay bolt                                     | 254 839        |     | e Disk                       | 259 647 |
| 23       | Guide of pressure cam complete                | 253 480        |     | f Washer                     | 022 893 |
| 34       | Loop sinking cam on the left complete E12-14  | 254 248        | 38  | Slider pressure cam complete | 251 834 |
| 35       | Loop sinking cam on the right complete E12-14 | 254 249        | 43  | Holding piece                | 251 828 |
| 36       | Rod guide on the left complete                | 252 662        | 503 | Cap screw M3x6               | 022 589 |
| 37       | Rod guide on the right complete               | 252 663        | 505 | Shim 0,5x12x75               | 236 654 |
| a        | Rod guide part                                | 258 148        | 509 | Pan head screw M3x4          | 023 142 |
| b        | Spring rod                                    | 252 661        | 511 | Shim 0,03x8x28               | 023 452 |
| c        | Compression spring                            | 257 082        | 512 | Shim 0,05x8x28               | 023 020 |




5.16.1 Cams E7.2 k&w

| Pos | Designation                                | Id      | Pos | Designation   | Id      |
|-----|--|---------|-----|---|---------|
| 2   | Entry cam on the left at the top           | 266 394 | 24  | Tuck pressure cam                                       | 253 828 |
| 3   | Entry cam on the right at the top          | 266 395 | 25  | Limiting cam E10   E7.2                                 | 251 993 |
| 4   | Entry cam at the top                       | 267 337 | 26  | Pointer E10   | 251 994 |
| 5   | Knitting position cam E10-14   E6.2   E7.2 | 255 021 | 27  | Screw   | 210 335 |
| 6   | Plate on the left E10-18                   | 255 389 | 28  | Stitch cam on the left E10-14   E7.2                    | 254 331 |
| 7   | Plate on the right E10-18                  | 255 390 | 29  | Stitch cam on the right E10-14   E7.2                   | 254 332 |
| 8   | Entry cam on the left E10-18               | 255 391 | 30  | Tuck limiting cam E10   E7.2                            | 254 295 |
| 9   | Entry cam on the right E10-18              | 255 392 | 31  | Raising cam plate E10-18                                | 251 992 |
| 10  | Pressure strip E10-14                      | 255 540 | 32  | Receiving cam E10-12                                    | 251 997 |
| 11  | Cam guide E10-18                           | 258 161 | 33  | Raising cam without split-stitch E10-12                 | 254 334 |
| 12  | Cam guide E10-18                           | 264 188 |     | Raising cam with split-stitch E10-12                    | 254 335 |
| 13  | Cam on the left E10-18                     | 255 613 | 39  | Cam at the right E10-18                                 | 259 769 |
| 14  | Cam at the right E10-18                    | 255 614 | 40  | Knitting position cam on the left E10-14   E6.2   E7.2  | 255 022 |
| 15  | Limiting cam on the left                   | 264 051 | 41  | Knitting position cam on the right E10-14   E6.2   E7.2 | 255 023 |
| 16  | Limiting cam on the right                  | 264 052 | 49  | Limiting cam middle                                     | 264 053 |
| 17  | Cam on the left E10-18                     | 259 768 | 50  | Delivery pressure cam                                   | 253 838 |
| 18  | Cam E10-18                                 | 258 152 | 51  | Offering cam  | 210 185 |
| 19  | Selection cam on the left E10-18           | 251 876 | 500 | Cap screw M4x8  | 020 091 |
| 20  | Selection cam on the right E10-18          | 251 877 | 510 | Cap screw M3x8  | 020 081 |
| 21  | Selection cam E10-18                       | 251 875 |     |   |         |




## 5.17 Cam box E8.2

| Pos      | Designation                                  | Id             | Pos | Designation                   | Id      |
|----------|--|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Cam box complete E8.2</b>                 | <b>265 747</b> |     |                               |         |
| 1        | Cam plate E10-18                             | 264 747        | 37  | d Circlip                     | 023 565 |
| 22       | Stay bolt                                    | 254 839        |     | e Disk                        | 259 647 |
| 23       | Guide of pressure part complete              | 253 480        |     | f Washer                      | 022 893 |
| 34       | Loop sinking cam on the left completeE16-18  | 251 965        | 38  | Slider pressure part complete | 251 834 |
| 35       | Loop sinking cam on the right completeE16-18 | 251 966        | 43  | Holding piece                 | 251 828 |
| 36       | Rod guide on the left complete               | 252 662        | 503 | Cap screw M3x6                | 022 589 |
| 37       | Rod guide on the right complete              | 252 663        | 505 | Shim0,5x12x75                 | 236 654 |
| a        | Rod guide part                               | 258 148        | 509 | Pan-head screw M3x4           | 023 142 |
| b        | Spring rod                                   | 252 661        | 511 | Shim0,03x8x28                 | 023 452 |
| c        | Compression spring                           | 257 082        | 512 | Shim0,05x8x28                 | 023 020 |




5.17.1 Cams E8.2

| Pos | Designation                              | Id      | Pos | Designation                                      | Id      |
|-----|--|---------|-----|--|---------|
| 2   | Entry cam on the left at the top E10-18  | 266 549 | 24  | Tuck pressure cam                                | 253 828 |
| 3   | Entry cam on the right at the top E10-18 | 266 590 | 25  | Limiting cam E8.2                                | 260 901 |
| 4   | Entry cam at the top E10-18              | 265 660 | 26  | Pointer E16-18                                   | 252 656 |
| 5   | Knitting position cam E16-18   E8.2      | 255 027 | 27  | Screw  | 210 335 |
| 6   | Plate on the left E10-18                 | 255 389 | 28  | Stitch cam on the left E16-18   E8.2             | 254 338 |
| 7   | Plate on the right E10-18                | 255 390 | 29  | Stitch cam on the right E16-18   E8.2            | 254 339 |
| 8   | Entry cam on the left E10-18             | 255 391 | 30  | Tuck limiting cam E8.2                           | 260 902 |
| 9   | Entry cam on the right E10-18            | 255 392 | 31  | Raising cam plate E10-18                         | 251 992 |
| 10  | Pressure strip E16-18                    | 256 681 | 32  | Receiving cam E8.2                               | 260 903 |
| 11  | Cam guide at the top E10-18              | 258 161 | 33  | Raising cam without split-stitch E16-18          | 254 340 |
| 12  | Cam guide E10-18                         | 264 188 |     | Raising cam with split-stitch E16-18             | 254 341 |
| 13  | Cam on the left E10-18                   | 255 613 | 39  | Cam at the right E10-18                          | 259 769 |
| 14  | Cam at the right E10-18                  | 255 614 | 40  | Knitting position cam on the left E16-18   E8.2  | 255 028 |
| 15  | Limiting cam on the left                 | 264 051 | 41  | Knitting position cam on the right E16-18   E8.2 | 255 029 |
| 16  | Limiting cam on the right                | 264 052 | 49  | Limiting cam middle                              | 264 053 |
| 17  | Cam on the left E10-18                   | 259 768 | 50  | Delivery pressure cam                            | 253 838 |
| 18  | Cam E10-18                               | 258 152 | 51  | Offering cam                                     | 210 185 |
| 19  | Selection cam on the left E10-18         | 251 876 | 500 | Cap screw M4x8                                   | 020 091 |
| 20  | Selection cam on the right E10-18        | 251 877 | 510 | Cap screw M3x8                                   | 020 081 |
| 21  | Selection cam E10-18                     | 251 875 |     |  |         |






## 6 Main take-down




## 6.1 Main Take-down

| Pos      | Designation                 | ID      | Pos | Designation   | ID      |
|----------|-----------------------------|---------|-----|---|---------|
| $\Sigma$ | <b>Main take-down</b>       |         |     |   |         |
| 1        | Main take-down on the left  | 253 851 | 3   | Main take-down in the middle<br>E10   E12   E14   E6.2   E7.2 | 253 525 |
| 2        | Main take-down on the right | 264 885 |     | Main take-down in the middle E16   E18   E8.2                 | 253 593 |




## 6.2 Main take-down on the left

| Pos      | Designation                         | Id             | Pos | Designation           | Id      |
|----------|-------------------------------------|----------------|-----|-----------------------|---------|
| <b>Σ</b> | <b>Main take-down on the left</b>   | <b>253 851</b> |     |                       |         |
| 2        | Bearing race complete               | 244 459        | 17  | Spring bolt           | 221 143 |
| 3        | Shaft on the left at the rear       | 221 012        | 19  | Stop point            | 252 503 |
| 5        | Bolts                               | 208 538        | 500 | Screw 50x15           | 251 728 |
| 7        | Mounting plate on the left complete | 231 725        | 504 | Washer 18             | 023 295 |
| 9        | Swivel-mounted bearing              | 251 761        | 505 | Retaining ring 18x1,2 | 020 955 |
| 10       | Full floating axle on the left      | 251 984        | 511 | Cap screw M6x12       | 020 134 |





## 6.3 Main take-down on the right

| Pos      | Designation                          | Id             | Pos | Designation              | Id      |
|----------|--------------------------------------|----------------|-----|--------------------------|---------|
| <b>Σ</b> | <b>Main take-down on the right</b>   | <b>264 885</b> |     |                          |         |
| 1        | Clutch set                           | 251 677        | 8   | Stop point               | 252 503 |
| 2        | Bearing race complete                | 244 459        | 500 | Screw 50x15              | 251 728 |
| 3        | Bolts                                | 208 538        | 501 | Washer 18                | 023 295 |
| 4        | Mounting plate on the right complete | 260 090        | 502 | Retaining ring 18x1,2    | 020 955 |
| 5        | Swivel-mounted bearing               | 251 761        | 503 | Cap screw M6x12          | 020 134 |
| 6        | Full floating axle on the right      | 251 985        | 504 | Microswitch Xgk2-s21 250 | 210 510 |
| 7        | Spring bolt                          | 221 143        | 505 | Cap screw M3x20          | 023 221 |




## 6.3.1 Mounting plate

| Pos        | Designation                                 | Id. no.        | Pos | Designation                  | Id. no. |
|------------|---|----------------|-----|------------------------------|---------|
| <b>Σ A</b> | <b>Mounting plate on the left complete</b>  | <b>231 725</b> | 2   | Shoulder screw               | 240 067 |
| 1          | Mounting plate on the left                  | 231 541        | 3   | Retaining plate on the right | 240 066 |
| 2          | Retaining plate on the left                 | 231 539        | 500 | Hexagon nut M4-6             | 022 536 |
| 500        | Pan-head screw M5x10                        | 023 247        | 501 | Microswitch                  | 026 259 |
| 501        | Serrated lock washer J5,3                   | 022 489        | 502 | Cap screw M3x16              | 022 583 |
| <b>Σ B</b> | <b>Mounting plate on the right complete</b> | <b>260 090</b> | 503 | Cap screw M5x8               | 244 278 |
| 1          | Mounting plate on the right                 | 260 067        | 504 | Washer 5-200                 | 020 871 |




## 6.3.2 Full floating axle on the left and the right

| Pos        | Designation                           | Id             | Pos        | Designation                            | Id             |
|------------|---------------------------------------|----------------|------------|--|----------------|
| <b>Σ L</b> | <b>Full floating axle on the left</b> | <b>251 984</b> | <b>Σ R</b> | <b>Full floating axle on the right</b> | <b>251 985</b> |
| 1          | Shaft on the left at the front        | 221 013        | 1          | Eccentric                              | 251 959        |
| 2          | Eccentric                             | 251 959        | 2          | Shaft on the right                     | 223 393        |
| 500        | Set collar                            | 020 938        | 3          | Gear wheel Z=40, M=2                   | 213 744        |
| 502        | Fitting freewheel ZZ6203L             | 023 294        | 500        | Fitting freewheel ZZ6203L              | 023 294        |
| 900        | Setscrew M6x8                         | 022 684        | 501        | Set collar                             | 020 938        |
|            |                                       |                | 502        | Setscrew M6x8                          | 022 684        |
|            |                                       |                | 503        | Feather key A 6x6x25                   | 023 017        |




## 6.4 Main take-down in the middle

| Pos      | Designation                            | ID             | Pos  | Designation                           | ID      |
|----------|--|----------------|------|---------------------------------------|---------|
| $\Sigma$ | <b>Main take-down in the middle</b>    |                | 13   | Take-down roller at the rear complete |         |
|          | E10   E12   E14   E6.2   E7.2          | <b>253 525</b> |      | E10   E12   E14   E6.2   E7.2         | 253 853 |
|          | E16   E18   E8.2                       | <b>253 593</b> |      | E16   E18   E8.2                      | 253 854 |
| 4        | Stripping angle at the rear complete   | 264 119        | 509  | Cap screw M8x25                       | 020 142 |
| 12       | Motor take-down unit complete          | 253 803        | 18*  | Stop point                            | 253 432 |
| 15       | Take-down roller at the front complete | 241 426        | 513* | Pan head screw M6x16                  | 023 124 |
| 20       | Connection cable winding plate         | 241 703        |      |                                       |         |




## 6.4.1 Stripper angle

| Pos      | Designation                                | Id             | Pos | Designation    | Id      |
|----------|--|----------------|-----|----------------|---------|
| <b>Σ</b> | <b>Stripper angle at the rear complete</b> | <b>264 119</b> |     |                |         |
| 1        | Stripper angle                             | 263 955        | 8   | Cam            | 260 109 |
| 3        | Axle                                       | 259 969        | 500 | Cap screw M5x8 | 023 319 |
| 5        | Bolts                                      | 228 310        | 501 | Setscrew M5x6  | 022 738 |
| 6        | Adjustment weight                          | 229 248        | 502 | Set collarA10  | 020 934 |




## 6.4.2 Rear take-down roller

| Pos      | Designation                                  | Id             | Pos | Designation       | Id      |
|----------|--|----------------|-----|-------------------|---------|
| <b>Σ</b> | <b>Take-down roller at the rear complete</b> |                | 6   | Ring on the right | 255 831 |
|          | E10   E12   E14   E6.2   E7.2                | <b>253 853</b> | 7   | Roller E5-14      | 264 624 |
|          | E16   E18   E8.2                             | <b>253 854</b> |     | Roller E16-18     | 231 400 |
| 1        | Ring on the left                             | 255 830        | 8   | Spacer slide      | 222 062 |
| 2        | Stop ring on the left                        | 204 369        | 9   | Brush             | 225 819 |
| 3        | Shaft  | 221 011        | 12  | Rod               | 253 301 |
| 4        | Stripper                                     | 241 612        | 500 | Dowel pin 6x32    | 020 685 |
| 5        | Spacer slide (E5-14)                         | 264 669        | 501 | Setscrew M8x16    | 258 910 |
|          | Spacer slide ( E16-18)                       | 240 104        |     |                   |         |




## 6.4.3 Front take-down roller

| Pos      | Designation                                   | Id             | Pos | Designation                | Id      |
|----------|---|----------------|-----|----------------------------|---------|
| $\Sigma$ | <b>Take-down roller at the front complete</b> | <b>241 426</b> | 4   | Locating piece             | 221 935 |
| 1        | Take-down roller at the front                 | 221 243        | 500 | Compression spring 1x10x30 | 023 741 |
| 2        | Angle rail complete                           | 241 425        | 501 | Cap screw M5x12            | 020 132 |
| 3        | Pressure sleeve                               | 220 911        | 502 | Washer 5-200               | 020 880 |




## 6.4.3.1 Front roller elements

| Pos      | Designation                          | Id             | Pos | Designation                           | Id      |
|----------|--------------------------------------|----------------|-----|---------------------------------------|---------|
| <b>Σ</b> | <b>Take-down roller at the front</b> | <b>221 243</b> |     |                                       |         |
| 1        | Bearing support on the left complete | 221 225        | 4   | Roller                                | 220 905 |
| aa       | Universal joint                      | 221 137        | 5   | Tube                                  | 221 092 |
| ab       | adaptor                              | 221 132        | 6   | Bearing support on the right complete | 221 240 |
| b        | Bearing support                      | 220 913        | aa  | Universal joint                       | 221 137 |
| c        | Gear wheel                           | 220 910        | ab  | adaptor                               | 221 132 |
| 501      | Spring dowel sleeve 4x20             | 023 551        | b   | Bearing support                       | 220 913 |
| 510      | Cap screw M5x20                      | 020 133        | c   | Gear wheel                            | 220 910 |
| 511      | Washer 5                             | 023 542        | 501 | Spring dowel sleeve 4x20              | 023 551 |
| 2        | Straps                               | 251 557        | 510 | Cap screw M5x20                       | 020 133 |
| 3        | Bearing support complete             | 221 241        | 511 | Washer 5                              | 023 542 |
| 3b       | Bearing support                      | 220 913        | 7   | Spacer pipe on the right              | 253 407 |
| 3a       | Gear wheel                           | 220 910        | 8   | Spacer pipe on the left               | 253 408 |
| 530      | Hexagon nut M5                       | 023 541        | 500 | Circlip                               | 021 025 |
| 531      | Washer 5-100hv                       | 023 542        |     |                                       |         |
| 532      | Cap screw M5x30                      | 022 396        |     |                                       |         |




## 6.4.3.2 Pressure angle rail

| Pos      | Designation                | Id             | Pos | Designation                     | Id      |
|----------|----------------------------|----------------|-----|---------------------------------|---------|
| <b>Σ</b> | <b>Angle rail complete</b> | <b>241 425</b> | 500 | Washer 6-200                    | 022 431 |
| 1        | Switch complete with cable | 221 265        | 501 | Hexagon nut M5-8                | 023 541 |
| 2        | Spring flange              | 242 327        | 502 | Compression spring 0,8x9,2x27,5 | 023 537 |
| 3        | Angle rail                 | 241 773        | 503 | Cap screw M2x12                 | 023 522 |
| 4        | Winding plate              | 221 101        | 504 | Washer 2-200                    | 022 908 |
| 5        | Retaining ring             | 242 325        | 505 | Shoulder screw M5x20x5          | 023 675 |




## 6.4.4 Impulse sensor and motor

| Pos      | Designation                          | Id             | Pos  | Designation     | Id      |
|----------|--------------------------------------|----------------|------|-----------------|---------|
| <b>Σ</b> | <b>Motor take-down unit complete</b> | <b>253 803</b> |      |                 |         |
| 1        | Asynchronous torque motor (complete) | 257 438        | 500  | Cap screw M4x8  | 022 501 |
| 2        | Impulse disc                         | 208 716        | 501  | Washer 4-200    | 020 879 |
| 3        | Light barrier take-down + comb       | 300 744        | 502  | Circlip         | 022 774 |
| 4        | Cover                                | 212 262        | 503  | Shim ring 4x8x1 | 023 369 |
| 5        | Gear wheel                           | 241 668        | 510* | Cap screw M8x25 | 020 142 |






## 7 Auxiliary Take-down




## 7.1 Auxiliary take-down pre-assembled

| Pos      | Designation                              | Id             | Pos  | Designation                    | Id      |
|----------|--|----------------|------|--------------------------------|---------|
| <b>Σ</b> | <b>Auxiliary take-down pre-assembled</b> | <b>254 061</b> |      |                                |         |
| 1        | Bearing on the right complete            | 239 996        | 14   | Lever at the rear on the right | 227 260 |
| 2        | Bearing on the left complete             | 239 999        | 15   | Toothed belt pulley complete   | 226 708 |
| 4        | Guide plate                              | 213 362        | 16   | Bolts                          | 227 914 |
| 5        | Metal angle on the left complete         | 225 013        | 17   | Protective plate               | 225 754 |
| 6        | Metal angle on the right complete        | 225 014        | 502  | Shoulder screw M3x27x32        | 023 634 |
| 9        | Toothed belt 10T5/260                    | 208 832        | 504  | Set collar                     | 020 934 |
| 10       | Take-down roller                         | 224 891        | 505  | Stop disk                      | 023 646 |
| 11       | Lever at the front on the left           | 227 263        | 506  | Spring dowel sleeve 3x20       | 020 776 |
| 12       | Lever at the front on the right          | 227 262        | 507  | Sheet metal screw St4,8x22-C   | 023 259 |
| 13       | Lever at the rear on the left            | 227 261        | 520* | Cap screw M6x16                | 020 135 |




7.1.1 Right bearing of the auxiliary take-down

| Pos      | Designation                              | Id             | Pos | Designation                  | Id                           |         |
|----------|--|----------------|-----|------------------------------|------------------------------|---------|
| <b>Σ</b> | <b>Bearing on the right complete</b>     | <b>239 996</b> |     | 531                          | Needle roller bearing HK1010 | 023 664 |
| 20       | Bearing block on the right               | 258 913        |     | 532                          | Slide bearing GFM-081014-06  | 023 358 |
| 21       | Cover                                    | 257 466        | 34  | Roller deflector             | 218 805                      |         |
| 22       | Drive shaft complete                     | 227 857        | 500 | Cap screw M3x16              | 022 560                      |         |
| 23       | Drive shaft complete                     | 227 853        | 510 | Cap screw M3x20              | 022 448                      |         |
| 24       | Gear wheel M=1,5, Z=20                   | 213 880        | 512 | Countersunk head screw M4x12 | 023 062                      |         |
| 25       | Gear wheel M=1,5, Z=20                   | 210 504        | 513 | Hexagon nut M6-6             | 020 836                      |         |
| 26       | Gear wheel on the right complete         | 218 524        | 514 | Threaded bolt with shoulder  | 243 226                      |         |
| 27       | Gear rack on the right                   | 253 487        | 515 | Shoulder screw M4x9x14       | 020 602                      |         |
| 28       | Threaded spacer                          | 229 683        | 516 | Setscrew M6x16-45            | 023 092                      |         |
| 29       | Sleeve                                   | 227 257        | 517 | Spiral pin 4x24              | 023 544                      |         |
| 30       | Sleeve                                   | 239 997        | 518 | Shim ring 4x8x0,5            | 023 384                      |         |
| 31       | Collar bolt                              | 210 551        | 519 | Shim ring 10x16x1,5          | 023 261                      |         |
| 32       | Cable with switch auxiliary take-downokc | 243 142        | 520 | Retaining ring 26x1,2        | 023 359                      |         |
| 33       | Connecting rod complete                  | 226 710        | 522 | Tension spring 7,5x0,7x28    | 023 595                      |         |
| 33a      | Connecting rod                           | 255 696        | 523 | Grooved ball bearing 6000-2Z | 022 599                      |         |




## 7.1.2 Left bearing of the auxiliary take-down

| Pos      | Designation                  | Id             | Pos | Designation                     | Id      |
|----------|------------------------------|----------------|-----|---------------------------------|---------|
| <b>Σ</b> | <b>Bearing on the left</b>   | <b>239 999</b> | 41  | Gear wheel on the left complete | 218 523 |
| 21       | Cover                        | 257 466        | 42  | Gear rack on the left           | 253 488 |
| 28       | Threaded spacer              | 229 683        | 510 | Cap screw M3x20                 | 022 448 |
| 30       | Sleeve                       | 239 997        | 512 | Countersunk head screw M4x12    | 023 062 |
| 31       | Collar bolt                  | 210 551        | 513 | Hexagon nut M6-6                | 020 836 |
| 33       | Connecting rod complete      | 226 710        | 514 | Threaded bolt with shoulder     | 243 226 |
| 33a      | Connecting rod               | 255 696        | 515 | Shoulder screw M4x9x14          | 020 602 |
| 530      | Slide bearing GFM-081014-06  | 023 358        | 516 | Setscrew M6x16-45               | 023 092 |
| 531      | Needle roller bearing HK1010 | 023 664        | 518 | Shim ring 4x8x0,5               | 023 384 |
| 34       | Roller deflector             | 218 805        | 519 | Shim ring 10x16x1,5             | 023 261 |
| 36       | Bearing block on the left    | 258 914        | 520 | Retaining ring 26x1,2           | 023 359 |
| 37       | Drive shaft complete         | 227 887        | 522 | Tension spring 7,5x0,7x28       | 023 595 |
| 39       | Bolts                        | 226 705        | 523 | Grooved ball bearing 6000-2Z    | 022 599 |




### 7.1.3 Metal angle on the left and right complete

| Pos        | Designation                             | Id             | Pos        | Designation                              | Id             |
|------------|---|----------------|------------|--|----------------|
| <b>Σ L</b> | <b>Metal angle on the left complete</b> | <b>225 013</b> | <b>Σ R</b> | <b>Metal angle on the right complete</b> | <b>225 014</b> |
| 1          | Metal angle on the left                 | 224 920        | 1          | Metal angle on the right                 | 224 931        |
| 2          | Roller deflector                        | 218 805        | 2          | Roller deflector                         | 218 805        |
| 3          | Fine rope                               | 224 977        | 3          | Fine rope                                | 224 977        |
| 4          | Sleeve                                  | 227 867        | 4          | Sleeve                                   | 227 867        |
| 500        | Cap screw M3x16                         | 022 560        | 500        | Cap screw M3x16                          | 022 560        |
| 501        | Hexagon nut M3-6                        | 022 564        | 501        | Hexagon nut M3-6                         | 022 564        |
| 502        | Shim ring 4x8x0,5                       | 023 384        | 502        | Shim ring 4x8x0,5                        | 023 384        |
| 503        | Spring washer A3                        | 021 005        | 503        | Spring washer A3                         | 021 005        |
| 507        | Tension spring 8x0,9x75                 | 021 287        | 507        | Tension spring 8x0,9x75                  | 021 287        |




## 7.2 Auxiliary take-down in the middle

| Pos      | Designation                                  | Id             | Pos | Designation     | Id      |
|----------|--|----------------|-----|-----------------|---------|
| $\Sigma$ | <b>Auxiliary take-down in the middle</b>     | <b>254 062</b> |     |                 |         |
| 3        | Take-down motor complete auxiliary take-down | 214 449        | 8   | Detent plate    | 222 040 |
| 7        | Shoulder screw                               | 207 101        | 500 | Cap screw M6x12 | 020 134 |




### 7.3 Motor

| Pos      | Designation                               | Id             | Pos  | Designation                      | Id      |
|----------|---|----------------|------|----------------------------------|---------|
| <b>Σ</b> | <b>Motor auxiliary take-down complete</b> | <b>214 449</b> |      |                                  |         |
| 1        | Motor auxiliary take-down                 | 213 871        | 500  | Cap screw M3x6                   | 022 589 |
| 2        | Motor bracket                             | 218 040        | 501  | Setscrew M6x10                   | 023 543 |
| 3        | Drive sleeve                              | 219 024        | 502  | Cap screw M5x55                  | 023 321 |
| 4        | Impulse disc                              | 218 449        | 503  | Compression spring 0,63x10,97x40 | 023 500 |
| 5        | Gear unit 4GN36K                          | 220 353        | 504  | Shim ring 6x12x1                 | 023 444 |
| 7        | Light barrier Auxiliary take-down         | 217 462        | 508  | Dowel pin5x28                    | 241 686 |
| 8        | Shaft                                     | 219 025        | 520* | Cap screw M6x12                  | 020 134 |




## 7.4 Yarn brake at clamping and cutting bed

| Pos        | Designation                   | Id             | Pos        | Designation                    | Id             |
|------------|-------------------------------|----------------|------------|--------------------------------|----------------|
| <b>Σ L</b> | <b>Yarn brake on the left</b> | <b>256 740</b> | <b>Σ R</b> | <b>Yarn brake on the right</b> | <b>256 715</b> |
| 1          | Cover on the left             | 256 739        | 3          | Cover on the right             | 256 714        |
| 2          | Leaf spring                   | 256 712        | 1          | Leaf spring                    | 256 712        |
| 3          | Test clamping plate           | 256 713        | 2          | Test clamping plate            | 256 713        |
| 500        | Cap screw M4x6                | 023 067        | 500        | Cap screw M4x6                 | 023 067        |




## 8 Comb Take-down



## 8.1 Comb Take-down


| Pos      | Designation                      | ID      | Pos | Designation                             | ID      |
|----------|----------------------------------|---------|-----|---|---------|
| $\Sigma$ | <b>Comb take-down</b>            |         |     | Comb take-down in the middle E10        | 253 589 |
| 1        | Comb take-down on the left       | 256 834 |     | Comb take-down in the middle E14   E7.2 | 253 590 |
| 2        | Comb take-down on the right      | 256 835 |     | Comb take-down in the middle E16   E8.2 | 253 591 |
| 3        | Comb take-down in the middle E12 | 253 522 |     | Comb take-down in the middle E18        | 253 592 |






## 8.3 Comb take-down on the right

| Pos      | Designation                                | Id             | Pos  | Designation                  | Id      |
|----------|--|----------------|------|------------------------------|---------|
| <b>Σ</b> | <b>Comb take-down on the right</b>         | <b>256 835</b> |      |                              |         |
| 1        | Clamping piece                             | 209 379        | 529  | Hexagon nut M8-6             | 020 838 |
| 2        | Pressure plate                             | 241 967        | 33   | Swivel lever on the right    | 252 858 |
| 3        | Bolts                                      | 222 152        | 36   | Clamping plate               | 227 159 |
| 5        | Toothed belt 16T10/1300                    | 240 065        | 500  | Cap screw M6x16              | 020 135 |
| 6        | Eccentric pin                              | 222 320        | 507  | Cap screw M6x65              | 240 162 |
| 12       | Drive shaft comb complete                  | 214 583        | 508  | Cap screw M6x45              | 022 689 |
| 14       | Toothed lock washer at the bottom complete | 211 822        | 511  | Hexagon nut M5-8             | 023 541 |
| 17       | Stay bolt                                  | 222 315        | 512  | Hexagon nut M5-6             | 020 835 |
| 18       | Stay bolt                                  | 240 056        | 513  | Hexagon nut M6-6             | 020 836 |
| 19       | Threaded rod M5                            | 240 057        | 514  | Hexagon nut M8-6             | 020 838 |
| 22       | Proximity switch inductive at the top      | 231 516        | 515  | Hexagon nut M16-6            | 020 845 |
| 23       | Proximity switch inductive at the bottom   | 231 520        | 517  | Washer 16                    | 020 876 |
| 24       | Light barrier complete                     | 256 825        | 530  | Tension spring 15x1,50x70,94 | 251 614 |
| 26       | Guide bar C35                              | 206 560        | 531  | Cap screw M6x12              | 020 134 |
| 27       | Rubber buffer                              | 206 561        | 532  | Washer 6                     | 020 872 |
| 29       | Comb guide on the right                    | 255 424        | 533* | Shim0,2x12x27                | 023 735 |
| 29a      | Driving bolt                               | 255 427        | 534* | Shim0,5x12x27                | 023 736 |
| 29b      | Angle                                      | 240 112        | 540* | Pan-head screw M5x10         | 023 247 |



### 8.3.1 Drive shaft of comb



| Pos      | Designation                            | Id             | Pos | Designation          | Id      |
|----------|--|----------------|-----|----------------------|---------|
| <b>Σ</b> | <b>Drive shaft comb complete</b>       | <b>214 583</b> |     |                      |         |
| 1        | Shaft                                  | 213 969        | 500 | Feather key A 6x6x25 | 023 017 |
| 2        | Gear wheel Z=40, M=2                   | 213 744        | 502 | Setscrew M6x8        | 022 684 |
|          | Always order position 502 additionally |                | 503 | Setscrew M6x12       | 023 898 |
| 3        | Toothed belt pulley at the top         | 206 394        | 504 | Set collar           | 020 938 |
|          | Always order position 503 additionally |                |     |                      |         |



8.3.2 Swivel lever comb take-down


| Pos        | Designation                      | Id             |
|------------|----------------------------------|----------------|
| <b>Σ L</b> | <b>Swivel lever on the left</b>  | <b>252 859</b> |
| 1          | Support                          | 252 780        |
| 2          | Shaft                            | 223 994        |
| 4          | Plunger                          | 255 650        |
| 5          | Swivel lever                     | 239 248        |
| 6          | Bolts                            | 214 053        |
| 7          | Eccentric bolt                   | 255 651        |
| 500        | Compression spring 1,4x13,6x93   | 023 572        |
| 501        | Spring dowel sleeve Iso8752-5x20 | 020 794        |
| 502        | Dowel pin5x22                    | 023 716        |
| 504        | Shoulder screwM5x29x35           | 251 618        |
| 505        | Shoulder screw M5x5,8x6,2        | 023 365        |
| 507        | Washer 10                        | 020 884        |
| 508        | Retaining ring                   | 020 950        |
| 509        | Shoulder screw M5x12x18          | 020 539        |
| 511        | Hexagon nut M8-6                 | 020 838        |
| <b>Σ R</b> | <b>Swivel lever on the right</b> | <b>252 858</b> |
| 1          | Support                          | 252 780        |
| 2          | Shaft                            | 238 339        |

| Pos | Designation               | Id      |
|-----|---------------------------|---------|
| 3   | Microswitch               | 026 259 |
| 4   | Plunger                   | 255 650 |
| 5   | Swivel lever              | 239 248 |
| 6   | Bolts                     | 214 053 |
| 7   | Angle                     | 224 009 |
| 8   | Angle                     | 238 304 |
| 9   | Eccentric bolt            | 255 651 |
| 500 | Pan-head screw M5x10      | 023 247 |
| 501 | Spring dowel sleeve 5x20  | 020 794 |
| 502 | Dowel pin5x22             | 023 716 |
| 503 | Spring dowel sleeve 5x12  | 020 793 |
| 504 | Shoulder screwM5x29x35    | 251 618 |
| 505 | Shoulder screw M5X5,8X6,2 | 023 365 |
| 506 | Cap screw M4x8            | 022 501 |
| 507 | Washer 10                 | 020 884 |
| 508 | Retaining ring10x1        | 020 950 |
| 509 | Shoulder screwM5X12X18    | 020 539 |
| 510 | Cap screw M3x16           | 022 583 |
| 511 | Washer 3                  | 020 877 |
| 513 | Hexagon nut M8-6          | 020 838 |




### 8.4 Comb take-down in the middle

| Pos      | Designation                         | ID      | Pos | Designation                   | ID      |
|----------|-------------------------------------|---------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Comb take-down in the middle</b> |         | 31  | Comb unit                     |         |
|          | E10                                 | 253 589 |     | E10                           | 241 533 |
|          | E12   E6.2                          | 253 522 |     | E12   E6.2                    | 240 061 |
|          | E14   E7.2                          | 253 590 |     | E14   E7.2                    | 241 534 |
|          | E16   E8.2                          | 253 591 |     | E16   E8.2                    | 241 535 |
|          | E18                                 | 253 592 |     | E18                           | 241 536 |
| 8        | Flange                              | 207 695 | 32  | Motor take-down unit complete | 253 803 |
| 9        | Shaft long                          | 213 968 | 35  | Marking plate                 | 259 237 |
| 500      | Cap screw M6x16                     | 020 135 | 502 | Cap screw M8x25               | 020 142 |
| 501      | Pan head screw M5x10                | 023 247 | 525 | Serrated lock washer J5,3     | 022 489 |




## 8.4.1 Comb unit

| Pos      | Designation                   | ID      | Pos | Designation                  | ID      |
|----------|-------------------------------|---------|-----|------------------------------|---------|
| <b>Σ</b> | <b>Comb unit</b>              |         | 5   | Hook slider                  |         |
|          | E10                           | 241 533 |     | E10                          | 220 996 |
|          | E12   E6.2                    | 240 061 |     | E12   E16   E6.2   8.2       | 220 994 |
|          | E14   E7.2                    | 241 534 |     | E14   E7.2                   | 220 993 |
|          | E16   E8.2                    | 241 535 |     | E18                          | 220 997 |
|          | E18                           | 241 536 | 7   | Collar bolt complete         | 211 036 |
| 1        | Hook bed                      |         | 8   | Cross slider                 | 213 429 |
|          | E10                           | 221 196 | 9   | Cover rail                   | 222 866 |
|          | E12   E6.2                    | 221 197 | 10  | Plunger                      | 205 678 |
|          | E14   E7.2                    | 221 198 | 11  | Switching lever complete     | 240 060 |
|          | E16   E8.2                    | 221 199 | 15  | Stabilizer                   | 215 253 |
|          | E18                           | 221 200 | 500 | Cap screw M4x12              | 022 664 |
| 2        | Closer                        |         | 502 | Countersunk head screw M5x12 | 023 340 |
|          | E10   E12   E14   E6.2   E7.2 | 230 106 | 504 | Hexagon nut M4-8             | 023 046 |
|          | E16   E18   E8.2              | 230 107 | 505 | Hexagon nut M5-04            | 020 854 |
| 3        | Body                          |         | 508 | Washer 5                     | 020 871 |
|          | E10   E12   E14   E6.2   E7.2 | 230 094 | 510 | Cap screw M4x35              | 023 550 |
|          | E16   E18   E8.2              | 230 095 | 511 | Circlip                      | 022 774 |
| 4        | Cover rail                    | 213 428 |     |                              |         |




8.4.2 Switching lever comb take-down

| Pos      | Designation                     | Id             | Pos | Designation             | Id      |
|----------|---------------------------------|----------------|-----|-------------------------|---------|
| $\Sigma$ | <b>Switching lever complete</b> | <b>240 060</b> | 500 | Cap screw M3x25         | 023 093 |
| 1        | Screw-on plate on the right     | 240 058        | 501 | Cap screw M4x20         | 023 171 |
| 2        | Screw-on plate on the left      | 240 059        | 502 | Cap screw M4x16         | 023 123 |
| 3        | Lever                           | 215 228        | 504 | Pan-head screw M6x12    | 023 435 |
| 4        | Bearing bolt                    | 215 675        | 505 | Pan-head screw M5x16    | 023 417 |
| 5        | Eccentric                       | 205 681        | 506 | Shim ring 16x22x2       | 023 449 |
| 6        | Tension cam                     | 215 287        | 507 | Shim ring 10x16x1       | 023 260 |
| 13       | Intermediate plate              | 213 980        | 510 | Hexagon nut M5          | 020 854 |
| 14       | Holding plate                   | 218 977        | 511 | Collar bearing 10x16x22 | 022 841 |
| 15       | Motor comb hook with 2 phases   | 244 635        | 515 | Threaded spacer         | 210 488 |






## 9 Belt Take-Down




## 9.1 Belt Take-Down

| Pos      | Designation                    | Id      | Pos | Designation                               | Id      |
|----------|--------------------------------|---------|-----|---|---------|
| <b>Σ</b> | <b>Belt take-down</b>          |         |     |   |         |
| 1        | Belt complete                  | 265 973 | 16  | Thread clamp                              | 267 514 |
| 2        | Drive unit complete            | 267 963 | 17  | Cable between switch and winding plate BA | 266 560 |
| 3        | Gear unit complete             | 265 979 | 500 | Cap screw M6x16                           | 020 135 |
| 4        | Left support complete          | 265 982 | 501 | Washer 6                                  | 020 872 |
| 5        | Winding guard complete         | 265 985 | 502 | Cap screw M6x25                           | 023 335 |
| 9        | Adapter yarn brake             | 236 177 | 503 | Countersunk screw M6x14                   | 266 777 |
| 10       | Yarn brake on the right E12-18 | 265 657 | 504 | Feather key 6x6x20                        | 265 788 |
| 11       | Yarn brake on the left E12-18  | 265 691 | 506 | Cap screw M6x8                            | 023 532 |
| 12       | Coupling                       | 265 693 | 507 | Cap screw M8x25                           | 023 563 |




## 9.2 Belt

| Pos      | Designation          | Id             | Pos | Designation             | Id      |
|----------|----------------------|----------------|-----|-------------------------|---------|
| <b>Σ</b> | <b>Belt complete</b> | <b>265 973</b> | 6   | Casing cap at the right | 266 382 |
| 1        | Drive shaft          | 265 607        | 7   | Casing cap at the left  | 266 383 |
| 2        | Bolts                | 265 633        | 8   | Support                 | 265 630 |
| 3        | Support body         | 265 608        | 500 | Screw 50x20             | 263 540 |
| 4        | Deflection rod       | 265 609        | 501 | Dowel pin 6x28          | 265 784 |
| 5        | Belt                 | 265 582        | 502 | Slide bearing           | 266 772 |




### 9.3 Drive unit

| Pos      | Designation                 | Id             | Pos | Designation                   | Id      |
|----------|-----------------------------|----------------|-----|-------------------------------|---------|
| <b>Σ</b> | <b>Drive unit complete</b>  | <b>265 975</b> |     |                               |         |
| 1        | Motor complete              | 265 614        | 8   | Toothed belt 560              | 265 738 |
| 2        | Plate at the top            | 266 818        | 500 | Retaining ring 20x1,2         | 020 956 |
| 3        | Motor support               | 266 819        | 501 | Grooved ball bearing 6204-2RS | 022 848 |
| 4        | Timing belt pulley 44-HTD8M | 265 624        | 502 | Grooved ball bearing 6004-2RS | 236 089 |
| 5        | Shaft                       | 265 634        | 503 | Cap screw M8x25               | 023 563 |
| 6        | Flange                      | 266 820        | 504 | Setscrew M16x12               | 023 898 |
| 7        | Eccentric                   | 266 612        | 505 | Feather key 6x6x20            | 265 788 |




## 9.4 Support on the left

| Pos      | Designation                  | Id             | Pos | Designation                       | Id                        |         |
|----------|------------------------------|----------------|-----|-----------------------------------|---------------------------|---------|
| <b>Σ</b> | <b>Left support complete</b> | <b>265 982</b> |     | 540                               | Cap screw M2x12           | 023 522 |
| 1        | Support angle                | 266 417        |     | 550                               | Switch of Winding PlateBA | 266 613 |
| 2        | Switch component complete    | 265 981        | 3   | Support                           | 266 418                   |         |
| 10       | Support on the left          | 266 821        | 4   | Holding angle at the left         | 265 704                   |         |
| 20       | Screw-on plate               | 266 419        | 5   | Bearing strip at the top complete | 266 825                   |         |
| 30       | Switch plate                 | 266 822        | 500 | Grooved ball bearing 6000-2Z      | 022 599                   |         |
| 40       | Operating shaft              | 266 823        | 501 | Cap screw M6x40                   | 020 140                   |         |
| 50       | Tension bar                  | 266 824        | 502 | Countersunk screw M4x12           | 023 062                   |         |
| 510      | Cap screw M4x8               | 022 501        | 503 | Cap screw M5x8                    | 023 319                   |         |
| 520      | Tension spring               | 023 308        | 504 | NutM6x8                           | 265 785                   |         |
| 530      | Compression spring           | 023 464        | 505 | Cap screw M3x8                    | 022 582                   |         |




## 9.5 Winding guard

| Pos      | Designation                                  | Id             | Pos | Designation         | Id      |
|----------|--|----------------|-----|---------------------|---------|
| $\Sigma$ | <b>Winding guard complete</b>                | <b>265 985</b> |     |                     |         |
| <b>A</b> | <b>Stripping angle at the rear complete</b>  | <b>265 983</b> | 4   | Shaft               | 265 697 |
| <b>B</b> | <b>Stripping angle at the front complete</b> | <b>265 984</b> | 500 | Dowel pin 2x10      | 266 722 |
| 1        | Stripping angle                              | 266 826        | 501 | Cap screw M5x8      | 023 319 |
| 2        | Stripping brush                              | 265 639        | 502 | Pan head screw M3x5 | 023 530 |
| 3        | Brush antistatic                             | 265 645        | 503 | Pan head screw M3x5 | 235 966 |




## 9.6 Yarn brakes

| Pos        | Designation                    | Id             | Pos | Designation         | Id      |
|------------|--------------------------------|----------------|-----|---------------------|---------|
| $\Sigma$ L | <b>Yarn brake on the left</b>  | <b>265 691</b> |     |                     |         |
| $\Sigma$ R | <b>Yarn brake on the right</b> | <b>265 657</b> | 2   | Leaf spring         | 256 712 |
| 1L         | Cover on the left              | 265 690        | 3   | Test clamping plate | 256 713 |
| 1R         | Cover on the right             | 265 656        | 500 | Cap screw M4x6      | 023 067 |






## 10 Yarn delivery device




### 10.1 Drive unit yarn carrier complete

| Pos      | Designation                             | ID             | Pos | Designation                  | ID      |
|----------|---|----------------|-----|------------------------------|---------|
| <b>Σ</b> | Drive unit yarn carrier complete        |                | 3   | YC-Rail 3, equipped (E16-18) | 264 212 |
|          | E10-14 (E12m.10   E14/12   E7.2   E8.2) | <b>257 994</b> |     | YC-Rail 3, equipped (E6.2)   | 267 193 |
|          | E16-18                                  | <b>263 803</b> | 4   | YC-Rail 4, equipped (E10-14) | 261 926 |
|          | E6.2                                    | <b>267 190</b> |     | YC-Rail 4, equipped (E16-18) | 264 213 |
| 1        | YC-Rail 1, equipped (E10-14)            | 257 997        |     | YC-Rail 4, equipped (E6.2)   | 267 194 |
|          | YC-Rail 1, equipped (E16-18)            | 264 210        | 7   | FF support                   | 261 526 |
|          | YC-Rail 1, equipped (E6.2)              | 267 191        | 9   | Stay bolt                    | 261 767 |
| 2        | YC-Rail 2, equipped (E10-14)            | 261 924        | 10  | Stop point complete          | 260 346 |
|          | YC-Rail 2, equipped (E16-18)            | 264 211        | 11  | Stop bolt                    | 259 818 |
|          | YC-Rail 2, equipped (E6.2)              | 267 192        | 500 | Cap screw M6x20              | 020 136 |
| 3        | YC-Rail 3, equipped (E10-14)            | 261 925        | 502 | Cap screw M4x10              | 023 136 |




## 10.2 YC rail, drive of operating shaft

| Pos | Designation             | ID      | Pos | Designation          | ID      |
|-----|-------------------------|---------|-----|----------------------|---------|
| 1   | Yarn carrier rail       | 266 605 | 20  | Bearing block        | 265 253 |
| 7   | Operating shaft         | 257 754 | 20a | Toothed belt         | 258 003 |
| 8   | Short coupling complete | 257 839 | 20b | Step motor           | 263 404 |
| 9   | Long coupling complete  | 257 838 | 20c | Card                 | 257 358 |
| 17  | Support                 | 257 813 | 26  | Yarn guide rod       | 264 209 |
| 18  | Support sheet           | 264 226 | 502 | Screw 35x10          | 251 729 |
| 19  | Fixing ring             | 257 811 | 504 | Pan head screw M4x10 | 023 450 |
|     |                         |         | 505 | Setscrew M3x3        | 263 507 |
|     |                         |         | 506 | Screw M4x12          | 023 367 |
|     |                         |         | 507 | Pan head screw M4x8  | 254 971 |




## 10.3 YC rail, drive

| Pos | Designation                          | ID      | Pos | Designation              | ID      |
|-----|--------------------------------------|---------|-----|--------------------------|---------|
| 10  | Toothed belt3M HP 5058               | 257 874 | 27  | Drive unit pre-assembled | 257 998 |
| 11  | Toothed belt3M HP 4860               | 257 873 | 28  | Bearing plate(1+3)       | 265 164 |
| 12  | Toothed belt3M HP 4758               | 257 872 |     | Bearing plate(2+4)       | 265 165 |
| 13  | Toothed belt3M HP 4563               | 257 871 | 29  | Bottom bearing(1+3)      | 265 166 |
| 14  | Support                              | 261 904 |     | Bottom bearing(2+4)      | 265 167 |
| 15  | Clamping plate                       | 257 817 | 30  | Bearing at the top (1+3) | 261 884 |
| 21  | Bearing of deflection roller track 1 | 265 154 |     | Bearing at the top (2+4) | 261 886 |
| 22  | Bearing of deflection roller track 2 | 265 155 | 500 | Cap screw M5x12          | 265 244 |
| 23  | Bearing of deflection roller track 3 | 265 156 | 501 | Cap screw M5x12-8.8      | 022 943 |
| 24  | Bearing of deflection roller track 4 | 265 157 | 503 | Dowel pin 3x6            | 245 292 |
| 25  | Adjusting screw                      | 261 905 | 508 | Washer 5                 | 259 666 |



## 10.4 Yarn carrier rails and carriages


| Pos            | Designation                | Pos | Designation         | ID      |
|----------------|----------------------------|-----|---------------------|---------|
| 1, 2, 3, 4     | Yarn carrier rail complete | 500 | Pan head screw M4x5 | 262 043 |
| 1A, 2A, 1B, 2B | Carriage of yarn carrier   |     |                     |         |



\*) E12m.10 | E14/12 | E7.2 | E8.2


### 10.5 Yarn guide system with 32 FKE ADF

| Pos      | Designation                             | ID             | Pos | Designation                 | ID      |
|----------|---|----------------|-----|-----------------------------|---------|
| <b>Σ</b> | <b>Yarn guide system 32 FKE 50" ADF</b> | <b>265 347</b> |     |                             |         |
| 1        | Profile complete                        | 266 219        | 10  | Support on the left         | 265 350 |
|          | 1a Support ADF                          | 266 216        | 11  | Sleeve                      | 263 525 |
|          | 1b Support ADF                          | 266 218        | 12  | Wedge                       | 265 353 |
|          | 1c Cover plate                          | 266 217        | 14  | Slot nut                    | 228 851 |
|          | 510 Screw 4x12                          | 253 153        | 16  | Connection cable FKE ADF    | 264 206 |
|          | 511 Screw M6x40                         | 266 246        | 17  | Yarn guide bracket complete | 241 581 |
| 2        | Support on the right                    | 263 508        | 18  | Yarn control unit           | 263 685 |
| 3        | Support on the left                     | 263 506        | 500 | Self-locking screw M6x12    | 023 415 |
| 4        | Rear left support                       | 263 509        | 501 | Serrated nut M6-10          | 023 414 |
| 5        | Rear right support                      | 263 510        | 502 | Square nut M8               | 023 269 |
| 6        | Yarn guide bar                          | 263 417        | 503 | Pan-head screw M8x16        | 023 113 |
| 8        | Yarn guide bar                          | 265 352        | 504 | Screw M6x20                 | 023 721 |
| 9        | Support right                           | 265 351        | 505 | Washer 8                    | 020 873 |
|          |   |                | 506 | Hammer-head nut M8          | 261 845 |




10.5.1 Yarn control unit ADF

| Pos      | Designation                   | Id             | Pos | Designation                      | Id      |
|----------|-------------------------------|----------------|-----|----------------------------------|---------|
| <b>Σ</b> | <b>Yarn control unit ADF</b>  | <b>263 685</b> |     |                                  |         |
| 1        | Lamp cap                      | 265 525        | 11  | Wire with eyelet                 | 265 533 |
| 2        | Tension arm                   | 265 526        | 12  | Rocker                           | 265 532 |
| 3        | Knot detector for large knots | 251 168        | 13  | Jack                             | 265 527 |
| 4        | Knot detector for mall knots  | 251 169        | 14  | Damper                           | 265 528 |
| 5        | Screw                         | 251 170        | 15  | Ceramic eyelet                   | 217 327 |
| 6        | Yarn brake disc               | 216 365        | 16  | Disk                             | 216 372 |
| 7        | Yarn holder for yarn brake    | 244 407        | 17  | Tension spring                   | 253 038 |
| 8        | Sleeve                        | 253 034        | 18  | Tension spring                   | 265 531 |
| 9        | Compression spring            | 253 035        | 19  | Compression spring of brake disk | 253 055 |
| 10       | Pin                           | 253 036        | 20  | Leg spring                       | 265 529 |






# 11 Fluff absorption




## 11.1 Fluff absorption

| Pos      | Designation             | ID      | Pos | Designation                           | ID      |
|----------|-------------------------|---------|-----|---------------------------------------|---------|
| <b>Σ</b> | <b>Fluff absorption</b> |         |     |                                       |         |
| 1        | Suction fan complete    | 259 446 | 4   | Suction device complete E16-18 (E8.2) | 263 587 |
| 2        | Suction hose 29x25x5200 | 266 267 |     | Suction device complete E10-14        | 263 586 |
| 3        | Suction hose 29x25x     | 263 572 | 500 | Cap screw M6x12                       | 265 565 |




## 11.2 Fluff absorption, carriage parts

| Pos      | Designation                        | ID                    | Pos                        | Designation              | ID               |
|----------|------------------------------------|-----------------------|----------------------------|--------------------------|------------------|
| <b>Σ</b> | <b>Fluff absorption</b>            |                       |                            |                          |                  |
| 1        | Lint container complete            | 263 568               | 2b                         | Suction tube support     | 263 563          |
|          | 1a Lint container                  | 263 559               |                            | 2c Bracket               | 255 627          |
|          | 1b Cover lint container            | 263 560               |                            | 520 Hexagon nut M3       | 020 831          |
|          | 1c Filter of lint container        | 263 561               |                            | 521 Screw KB30x6         | 241 424          |
|          | 1d Support of lint container       | 259 832               |                            | 522 Pan-head screw M3x10 | 023 032          |
|          | 510 Pan-head screw M4x30           | 023 681               |                            | 3                        | Suction tube bar |
|          | 511 Pan-head screw M4x8            | 254 971               | 530 Setscrew M4x6          |                          | 023 277          |
| 2        | Suction tube complete E10-14       | 263 565               | 500 Suction hose 25x20x220 | 263 567                  |                  |
|          | Suction tube complete E16-18 (8.2) | 263 566               | 501 Pan-head screw M5x8    | 239 408                  |                  |
|          | 2a                                 | Suction tube complete | 263 569                    | 502 Cap screw M5x12      | 263 572          |






## 12 Operation and control




### 12.1 Starting device

| Pos      | Designation                       | Id             | Pos | Designation                    | Id      |
|----------|-----------------------------------|----------------|-----|--------------------------------|---------|
| <b>Σ</b> | <b>Starting device complete</b>   | <b>262 163</b> | 16  | Connection cable of covers     | 264 128 |
| 1        | Engaging rod                      | 262 164        | 17  | Termination plug of covers     | 256 896 |
| 2        | Bearing on the left complete      | 262 165        | 18  | Guide rail at the top complete | 264 126 |
| 3        | Guide rail at the bottom complete | 264 140        | 19  | Slot nut                       | 264 280 |
| 4        | Bearing on the right complete     | 265 444        | 20  | Snap rivet                     | 256 684 |
| 5        | Switch with cable to safety doors | 223 350        | 21  | Cover strip                    | 264 246 |
| 6        | Locating bolt                     | 219 107        | 22  | Cover strip                    | 264 247 |
| 7        | Slot nut                          | 225 099        | 23  | Cover strip                    | 264 248 |
| 8        | Front profile at the bottom       | 264 137        | 25  | Slot nut for front profile     | 265 373 |
| 9        | Slot nut for front profile        | 262 204        | 26  | Bearing on the right           | 265 402 |
| 10       | Bar for switches                  | 264 170        | 500 | Screw M6x25                    | 023 510 |
| 11       | Threaded spacer                   | 261 782        | 501 | Cap screw M6x16                | 020 135 |
| 12       | Shim for switch                   | 256 861        | 502 | Pan-head screw M5x14           | 023 588 |
| 13       | Card safety door switch middle    | 256 666        | 503 | Cap screw M6x20                | 020 136 |
| 14       | Card safety door switch outside   | 256 667        | 507 | Cap screw M6x10                | 023 690 |
| 15       | Cable of cover ADF                | 264 181        | 509 | Cap screw M4x16                | 020 131 |




### 12.1.1 Bearing of the engaging rod

| Pos      | Designation                         | ID             | Pos      | Designation                          | ID      |
|----------|-------------------------------------|----------------|----------|--------------------------------------|---------|
| <b>L</b> | <b>Bearing on the left complete</b> | <b>262 165</b> | 504      | Adhesive magnet direct current       | 026 233 |
| 1        | Bearing on the left                 | 262 167        | 505      | Hexagon nut M8-6                     | 020 838 |
| 1a       | Clip bearing MCM 12-04              | 023 639        | 506      | Dowel pin 1,5x8                      | 236 923 |
| 2        | Support of buffer                   | 220 561        | 507      | Spring dowel sleeve 6x20             | 023 719 |
| 2a       | O-ring 14x4                         | 023 237        | 508      | Shoulder screw M4x24,8x7,7           | 240 299 |
| 3        | Shaft on the left                   | 245 219        | 509      | Shoulder screw                       | 251 316 |
| 4        | Anchor                              | 253 776        | 510      | Shim ring 12x18x1                    | 023 315 |
| 5        | Switch flag                         | 245 220        | 511      | Retaining ring 12x1                  | 020 951 |
| 6        | Spring mandrel                      | 251 340        | 512      | Compression spring 1,25x15x98,2      | 023 609 |
| 7        | Disk                                | 245 222        | 513      | Compression spring 0,5x11x12         | 251 369 |
| 8        | Shoulder screw                      | 254 528        |          |                                      |         |
| 500      | Cap screw M4x6                      | 023 067        | <b>R</b> | <b>Bearing on the right complete</b> |         |
| 501      | Cap screw M4x8                      | 022 501        | 26       | Bearing on the right                 | 265 402 |
| 502      | Shim ring 4x8x1                     | 023 369        | 26a      | Clip bearing MCM 12-04               | 023 639 |
| 503      | Card engaging                       | 259 000        | 40       | Bearing on the right complete        | 265 444 |




## 12.2 Input unit

| Pos      | Designation                | Id             | Pos | Designation                        | Id      |
|----------|----------------------------|----------------|-----|------------------------------------|---------|
| <b>Σ</b> | <b>Input unit complete</b> | <b>263 649</b> | 8   | Shoulder screw                     | 264 179 |
| 1        | Display casing             | 263 394        | 9   | Depositing shell                   | 264 197 |
| 2        | Sheet metal guiding        | 264 166        | 503 | Screw 60x20-Z                      | 243 625 |
| 3        | Sheet metal at the front   | 264 141        | 504 | Pan-head screw M4x6                | 023 427 |
| 4        | Collar bolt                | 220 468        | 505 | Shim ring 10x16x1                  | 023 260 |
| 5        | Roll                       | 220 463        | 506 | Oval flange head screw M4x5        | 262 043 |
| 6        | Roll                       | 264 180        | 20* | Energy chain display               | 263 640 |
| 7        | Earth cable of display     | 262 487        | 21* | Depositing gutter of display chain | 265 576 |




### 12.3 Control of Collecting Area

| Pos      | Designation               | Id             | Pos      | Designation                   | Id             |
|----------|---------------------------|----------------|----------|-------------------------------|----------------|
| <b>Σ</b> | <b>Reflector complete</b> | <b>256 826</b> | <b>Σ</b> | <b>Light barrier complete</b> | <b>256 825</b> |
| 1        | Mounting plate reflector  | 256 675        | 1        | Holding angle light barrier   | 256 674        |
| 500      | Blind rivet A3x8-Al       | 023 158        | 500      | Cap screw M3x10               | 022 991        |
| 501      | Reflector 20x20 mm        | 243 356        | 501      | Light Barrier                 | 243 355        |
| 900*     | Cap screw M6x12           | 020 134        | 900*     | Cap screw M6x12               | 020 134        |
|          |                           |                | 901*     | Washer 6                      | 020 872        |




## 12.4 Signal light

| Pos      | Designation                  | Id             | Pos | Designation | Id |
|----------|------------------------------|----------------|-----|-------------|----|
| <b>Σ</b> | <b>Signal light LED</b>      | <b>240 395</b> |     |             |    |
| 500      | Pan head screw M4x14         | 023 037        |     |             |    |
| 501      | Serrated lock washer A4,3-FS | 022 482        |     |             |    |




## 12.5 Shock stop motion E10 | E12 | E14 | E6.2 | E7.2

| Pos      | Designation                   | ID             | Pos  | Designation           | ID      |
|----------|-------------------------------|----------------|------|-----------------------|---------|
| <b>Σ</b> | Shock stop motion complete E3 | <b>241 819</b> |      |                       |         |
| 1        | Shock stop motion (Piezo)     | 220 011        | 10*  | Cable piezo NB OKC    | 240 518 |
| 2        | Connecting cable piezo sensor | 220 061        | 500* | Pan head screw M4x8   | 023 036 |
| 3        | End plug piezo sensor         | 220 053        | 502* | Cable clip N-3B, 5 mm | 210 729 |




## 12.6 Shock stop motion E16|18 | E8.2

| Pos      | Designation                   | Id             | Pos  | Designation            | Id      |
|----------|-------------------------------|----------------|------|------------------------|---------|
| <b>Σ</b> | Shock stop motion complete E3 | <b>250 384</b> | 4    | Cable connection piezo | 250 295 |
| 1        | Shock stop motion (Piezo)     | 220 011        | 10*  | Cable piezo            | 240 518 |
| 2        | Cable connection piezo        | 250 291        | 500* | Pan-head screw M4x8    | 023 036 |
| 3        | End plug piezo sensor         | 220 053        | 502* | Cable clip N-3B, 5 mm  | 210 729 |




## 12.7 Measuring device

| Pos      | Designation              | Id      | Pos | Designation                    | Id      |
|----------|--------------------------|---------|-----|--------------------------------|---------|
| <b>Σ</b> | <b>Measuring device</b>  |         | 15  | Impulse sensor GLM OH complete | 264 314 |
| 1        | Measuring bar            | 264 957 | 507 | Screw 60x20                    | 243 625 |
| 4        | Guide outside            | 251 605 | 511 | Cap screw M5x10                | 022 918 |
| 7        | Support of measuring bar | 258 000 | 513 | Hexagon nut M6-04              | 257 088 |
| 10       | Setscrew                 | 230 803 | 530 | Setscrew                       | 230 803 |






## 13 Protective devices




### 13.1 Lateral safety doors

| Pos       | Designation                               | Id             | Pos | Designation | Id      |
|-----------|---|----------------|-----|-------------|---------|
| <b>ΣL</b> | <b>Safety door on the left complete</b>   | <b>263 318</b> |     |             |         |
| 1L        | Safety door on the left                   | 263 311        | 4   | Actuator    | 263 217 |
| <b>ΣR</b> | <b>Safety door on the right complete.</b> | <b>263 319</b> | 5   | Cover plate | 263 980 |
| 1R        | Safety door on the right                  | 263 312        | 500 | Screw 6x12  | 263 996 |
| 2         | Hinge                                     | 263 216        | 501 | Screw 50x20 | 263 540 |
| 3         | Locking plate                             | 219 748        | 502 | Screw 4x16  | 263 995 |




## 13.2 Panelling

| Pos | Designation       | Id      | Pos       | Designation   | Id      |
|-----|-------------------|---------|-----------|---|---------|
| 1   | Cover 1 complete  | 264 145 | <b>ΣL</b> | <b>Control unit panelling on the left complete</b>  | 263 608 |
|     | 1a   Cover 1+4    | 264 143 |           | 11   Side part                                      | 263 825 |
| 2   | Cover 2 complete  | 264 146 |           | 12L   Control unit panelling on the left            | 263 810 |
|     | 2a   Cover 2+3    | 264 144 |           | 13   Hinge  | 263 814 |
| 3   | Cover 3 complete  | 264 147 |           | 500   Cap screw M6x10                               | 023 690 |
|     | 3a   Cover 2+3    | 264 144 | <b>ΣR</b> | <b>Control unit panelling on the right complete</b> | 263 609 |
| 4   | Cover 4 complete  | 264 148 |           | 11   Side part                                      | 263 825 |
|     | 4a   Cover 1+4    | 264 143 |           | 12R   Control unit panelling on the right           | 263 811 |
| b   | Inlet type handle | 251 376 |           | 13   Hinge  | 263 814 |
| c   | Stripper          | 264 142 |           | 500   Cap screw M6x10                               | 023 690 |
| d   | Magnet            | 256 801 |           |   |         |




## 13.3 Covers

| Pos       | Designation                       | Id             | Pos       | Designation                        | Id             |
|-----------|-----------------------------------|----------------|-----------|------------------------------------|----------------|
| <b>ΣL</b> | <b>Cover on the left complete</b> | <b>263 755</b> | <b>ΣR</b> | <b>Cover on the right complete</b> | <b>263 756</b> |
| 1L        | Cover on the left                 | 264 040        | 1R        | Cover on the right                 | 264 041        |
| 2         | Rear sheet metal support          | 263 224        | 2         | Rear sheet metal support           | 263 224        |
| 3         | Front sheet metal support         | 263 759        | 3         | Front sheet metal support          | 263 759        |
| 500       | Pan-head screw M5x12              | 023 262        | 500       | Pan-head screw M5x12               | 023 262        |




## 13.4 Light curtain

| Pos      | Designation                          | Id             | Pos | Designation                           | Id      |
|----------|--------------------------------------|----------------|-----|---------------------------------------|---------|
| <b>Σ</b> | <b>Safety light curtain complete</b> | <b>264 277</b> | 4   | Right yoke                            | 264 780 |
| 1        | Safety light curtain cascade         | 264 266        | 7   | Connection cable of light curtain ADF | 264 271 |
| 2        | Safety light curtain ending device   | 264 267        | 500 | Cap screw M6x16                       | 020 135 |
| 3        | Yoke on the Left                     | 264 779        | 501 | Washer 6                              | 022 431 |




## 13.5 Left table

| Pos      | Designation                         | Id             | Pos | Designation                | Id      |
|----------|-------------------------------------|----------------|-----|----------------------------|---------|
| <b>Σ</b> | <b>Left table complete</b>          | <b>264 238</b> | 10  | Roller guide in the middle | 265 169 |
| 1        | Left table                          | 264 081        | 500 | Hexagon nut M4             | 020 853 |
| 2        | Roller guide in the middle complete | 263 621        | 501 | Hexagon nut M8             | 022 843 |
| 3        | Roller guide in the middle complete | 263 622        | 502 | Cap screw M5x16            | 022 726 |
| 4        | Roller guide at the top complete    | 263 624        | 503 | Cap screw M5x10            | 022 918 |
| 5        | Roller guide at the bottom complete | 263 631        | 504 | Washer 8                   | 020 871 |
| 6        | Positioning pin                     | 204 819        | 505 | Washer 8                   | 020 873 |
| 7        | Bumper                              | 263 006        | 506 | Serrated washer 5          | 020 901 |
| 8        | Retaining plate                     | 265 732        | 507 | Pan-head screw M5x25       | 259 834 |
| 9        | Guide bolt                          | 264 332        | 508 | Hexagon nut M5             | 023 541 |




## 13.6 Right table

| Pos      | Designation                         | Id             | Pos | Designation                | Id      |
|----------|-------------------------------------|----------------|-----|----------------------------|---------|
| <b>Σ</b> | <b>Right table complete</b>         | <b>264 239</b> |     |                            |         |
| 1        | Right table                         | 264 078        | 14  | Foam rubber stripes        | 263 544 |
| 2        | Roller guide in the middle complete | 263 621        | 15  | Roller guide in the middle | 265 169 |
| 3        | Roller guide in the middle complete | 263 622        | 500 | Hexagon nut M4             | 020 853 |
| 4        | Roller guide at the top complete    | 263 624        | 501 | Hexagon nut M8             | 022 843 |
| 5        | Roller guide at the bottom complete | 263 631        | 502 | Cap screw M5x16            | 022 726 |
| 6        | Positioning pin                     | 204 819        | 503 | Pan-head screw M6x10       | 023 666 |
| 7        | Bumper                              | 263 006        | 504 | Washer 5                   | 020 871 |
| 8        | Safety sash fastener of cabinet     | 265 970        | 505 | Washer 6                   | 020 872 |
| 10       | Locking bar                         | 264 096        | 506 | Washer 8                   | 020 873 |
| 11       | Guide bolt                          | 264 332        | 507 | Serrated washer 5          | 020 901 |
| 12       | Roller guide in the middle complete | 266 592        | 508 | Pan-head screw M5x25       | 259 834 |
| 13       | Foam rubber stripes                 | 263 547        | 509 | Hexagon nut M5             | 023 541 |




### 13.7 Table left and right, rollers

| Pos       | Designation                         | Id      | Pos        | Designation                         | Id      |
|-----------|-------------------------------------|---------|------------|-------------------------------------|---------|
| <b>Σ2</b> | Roller guide in the middle complete | 263 621 | <b>Σ5</b>  | Roller guide at the bottom complete | 263 631 |
|           | 21 Roll                             | 263 016 |            | 51 Bearing bolt                     | 262 997 |
|           | 22 Bolts                            | 263 015 | <b>Σ10</b> | Roller guide in the middle          | 265 169 |
|           | 23 Support                          | 264 085 |            | 103 Roll                            | 265 060 |
| <b>Σ3</b> | Roller guide in the middle complete | 263 622 | 500        | Shim ring 5x10x1,5                  | 023 348 |
|           | 31 Bolts                            | 263 012 | 501        | Retaining ring 5x0,6                | 023 347 |
|           | 32 Support                          | 264 089 | 502        | Hexagon nut M8                      | 022 843 |
|           | 33 Roll                             | 262 998 | 510        | Shim ring 8x14x0,5                  | 023 501 |
| <b>Σ4</b> | Roller guide at the top complete    | 263 624 | 511        | Hexagon nut M8                      | 022 843 |
|           | 41 Bearing bolt                     | 263 478 | 512        | Retaining ring 8x0,8                | 020 949 |
|           | 42 Roll                             | 262 999 | 513        | Washer 8                            | 020 873 |



## 14 Electrical equipment










## 14.1 Circuit diagram (222) as PDF

| Designation                 | ID      | Marking |
|-----------------------------|---------|---------|
| Circuit diagram 222 German  | 257 280 | _DE     |
| Circuit diagram 222 English | 257 280 | _GB     |
| Circuit diagram 222 Chinese | 257 280 | _CN     |



You will find the circuit diagram 222 on the CMS documentation DVD with the ID no. 257 157








### 14.2 Cable guide front and rear ADF

| Designation   |   | ID             | Designation   |                                       | ID      |
|---|---|----------------|---|---------------------------------------|---------|
| <b>Σ Front cable guide complete ADF</b>   |   | <b>258 279</b> |   |                                       |         |
| 1   | Cable impulse sensor 2 at the front XR137 ADF | 265 522        | 2   | Cable carriage at the front XR333 ADF | 265 520 |
|  |   |                |   |                                       |         |
| <b>Σ Rear cable guide complete ADF</b>  |   | <b>258 280</b> |   |                                       |         |
| 1   | Cable impulse sensor 2 at the rear XR136 ADF  | 265 521        | 2   | Cable carriage at the rear XR332 ADF  | 265 519 |
|  |   |                |  |                                       |         |










## 14.3 Cable set installation

| Designation   |                                      | Id             | Designation  |                            | Id      |
|---|--------------------------------------|----------------|--|----------------------------|---------|
| $\Sigma$  | <b>Cable set installation AFDF</b>   | <b>259 103</b> |  |                            |         |
| 1   | Loom of cables base 1 AFDF           | 259 104        | 3  | Loom of cables 5XX AFDF    | 263 750 |
| 2   | Loom of cables base 2AFDF            | 259 105        | 4  | Loom of cables comb OKC    | 240 259 |
|   |                                      |                |  |                            |         |
| 6   | Cable switch main take-down 50" ECO2 | 252 541        | 7  | Cable supply FKE lamp ECO2 | 252 587 |
|  |                                      |                |  |                            |         |






14.3.1 Cable set base 1 AFDF

| Designation   |   | Id             | Designation  |                       | Id      |
|---|---|----------------|--|-----------------------|---------|
| <b>Σ</b>  | Loom of cables base 1 AFDF              | <b>259 104</b> |  |                       |         |
| 1   | Cable feed wheel on the left 50" OKC    | 240 464        | 4  | Cable CAN 72" OKC     | 240 460 |
|  |   |                |  |                       |         |
| 2   | Cable Engaging rod ECO2                 | 252 538        | 5  | Cable +40 servo AFDF  | 259 107 |
|  |   |                |  |                       |         |
| 3   | Cable protective device on the left 5XX | 264 750        | 6  | Cable data servo AFDF | 259 108 |
|  |   |                |  |                       |         |






## 14.3.2 Loom of cables base 2 AFDF

| Designation   | Id             | Designation   | Id      |
|---|----------------|---|---------|
| <b>Σ Loom of cables base 2 AFDF</b>   | <b>259 105</b> |   |         |
| 1 Cable motor HAAB OKC  | 240 291        | 6 Cable racking motor OKC 3XX   | 240 297 |
|    |                |   |         |
| 2 Cable racking limit switch OKC 3XX  | 240 292        | 7 Cable resolver racking OKC 3XX  | 240 298 |
|    |                |   |         |
| 3 Fan cable of Main Drive Motor AFDF  | 261 712        | 8 Cable drive motor AFDF  | 259 109 |
|    |                |   |         |
| 4 Cable Feed wheel on the right OKC 3XX   | 240 294        | 9 Cable resolver drive AFDF   | 259 110 |
|   |                |  |         |
| 5 Cable protective device on the right 5XX  | 264 751        |   |         |
|  |                |   |         |





14.3.3 Loom of cables 5XX ADF

| Designation   | Id             | Designation   | Id      |
|---|----------------|---|---------|
| <b>Σ Loom of cables 5XX ADF</b>   | <b>263 750</b> |   |         |
| Cable motor auxiliary take-down 50" okc   | 240 467        | Cable power supply unit of mains supply OKC   | 240 505 |
|    |                |   |         |
| Cable impulse sensor auxiliary take-down 50" OKC                                    | 240 468        | Cable switch auxiliary take-down 3xx OKC  | 240 472 |
|    |                |   |         |
| Cable power supply WAZ/F 50" OKC  | 263 686        | Cable power supply FLENT 50" OKC  | 251 231 |
|   |                |  |         |
| Cable power supply servo 50" OKC  | 240 502        |   |         |
|  |                |   |         |





## 14.3.4 Loom of cables comb

| Designation   | Id             | Designation  | Id      |
|---|----------------|--|---------|
| <b>Σ</b> Loom of cables comb OKC  | <b>240 259</b> |  |         |
| Cable motor comb hookOKC  | 240 308        | Cable switch combOKC   | 240 311 |
|    |                |  |         |
| Cable switch KAHA OKC   | 240 309        | Cable switch HAAB OKC  | 240 312 |
|    |                |  |         |
| Cable motor combOKC   | 240 310        |  |         |
|  |                |  |         |

### 14.4 Loom of cables servo AFDF left 32-fold


| Designation   | Id             | Designation   | Id      |
|---|----------------|---|---------|
| <b>Σ Loom of cables servo AFDF left 32-fold</b>                                   | <b>259 352</b> |   |         |
| 1 Cable left servo motor AFDF front 1   | 259 178        | 7 Cable SM left AFDF front 1  | 259 195 |
| 2 Cable left servo motor AFDF front 4   | 259 181        | 8 Cable SM left AFDF rear 4   | 259 198 |
|  |                |   |         |
| 3 Cable resolver left AFDF front 1/1  | 259 187        | 9 Cable angle sensor left AFDF front 1  | 259 203 |
| 4 Cable resolver left AFDF front 1/2  | 259 343        | 1 Cable angle sensor left AFDF rear 4   | 259 206 |
| 5 Cable resolver left AFDF rear 4/1   | 259 190        | 0   |         |
| 6 Cable resolver left AFDF rear 4/2   | 259 346        |  |         |
|  |                |   |         |

## 14.5 Loom of cables servo AFDF right 32-fold

| Designation  | Id             | Designation  | Id      |                                       |         |   |         |
|--|----------------|--|---------|---------------------------------------|---------|---|---------|
| <b>Σ Loom of cables servo AFDF right 32-fold</b>                                   | <b>259 354</b> |  |         |                                       |         |   |         |
| 1 Cable right servo motor AFDF front 1   | 259 183        | 7 Cable SM right AFDFfront 1   | 259 199 |                                       |         |   |         |
| 2 Cable right servo motor AFDF front 4   | 259 186        | 8 Cable SM right AFDF rear 4   | 259 202 |                                       |         |   |         |
|   |                |  |         |                                       |         |   |         |
|  |                |  |         | 3 Cable resolver right AFDF front 1/1 | 259 191 | 9 Cable angle sensor right AFDF front 1   | 259 207 |
|  |                |  |         | 4 Cable resolver right AFDF front 1/2 | 259 347 | 10 Cable angle sensor right AFDF rear 4   | 259 210 |
|  |                |  |         | 5 Cable resolver right AFDF rear 4/1  | 259 194 |  |         |
|  |                |  |         | 6 Cable resolver right AFDF rear 4/2  | 259 350 |   |         |
|  |                |  |         |                                       |         |   |         |




## 15 Control electronics




## 15.1 Right control cabinet

| Pos      | Designation                                      | Id             | Pos | Designation                        | Id      |
|----------|--|----------------|-----|------------------------------------|---------|
| <b>Σ</b> | <b>Control unit on the right complete ADF</b>    | <b>259 043</b> | 6   | Card BIO ADF                       | 301 036 |
| 1        | Control unit on the right without equipment AFDF | 259 044        | 7   | Card final stages 4SM 7TE          | 300 943 |
|          | 521 Axial blower Servo 5                         | 229 059        | 8   | Card N-CPU 432F                    | 301 014 |
| 2        | Power supply unit CG54                           | 300 923        | 9   | Card Power CPU B                   | 301 009 |
| 3        | Battery plug-in unit                             | 301 008        | 10  | Card IPC P12 XP                    | 301 039 |
| 4        | Card Servo 6                                     | 301 000        | 14  | Safety relay for light curtain     | 264 233 |
| 5        | Card C-WAZ ECO2                                  | 301 006        | 20* | Cable of battery plug-in unit ECO2 | 252 375 |



## 15.2 Left control cabinet


| Pos      | Designation   | Id             | Pos | Designation                 | Id      |
|----------|---|----------------|-----|-----------------------------|---------|
| $\Sigma$ | <b>Control unit on the left complete</b> ADF        | <b>259 045</b> | 2   | Card servoFF                | 301 013 |
| 1        | Control unit on the left without equip-<br>mentAFDF | 259 046        | 3   | Power supply card 40 V AFDF | 301 036 |






## 16 Deliverable accessories

You can order the following tools, lubricants and expendables. The following list does not correspond to the scope of delivery of the knitting machine.




### 16.1 Accessories part 1

| Pos      | Designation                           | Id             | Pos | Designation              | Id      |
|----------|---------------------------------------|----------------|-----|--------------------------|---------|
| <b>Σ</b> | <b>Accessories standard part 1</b>    | <b>265 182</b> |     |                          |         |
| 2        | Extraction hook                       | 232 027        | 8   | Working hook             | 227 249 |
| 2a       | Small pin                             | 202 843        | 9   | Fuse 3,15A T/440V 6,3x32 | 025 261 |
| 2b       | Pencil                                | 232 022        | 10  | Fuse 6,3A T/440V 6,3x32  | 026 809 |
| 3        | Grease Stoll Grease 0475, 150g        | 270 721        | 11  | Fuse 10A T/440V 6,3x32   | 025 258 |
| 4        | Textile machine oil Stolltex T 46, 1l | 268 621        | 12  | Fuse 2,5A T/440V 6,3x32  | 217 465 |
| 5        | Oil combifix                          | 216 732        | 13  | Fuse 1A T/440V 6,3x32    | 209 321 |
| 6        | Measuring tape L=150cm                | 228 180        | 14  | Fuse 1,6A T 5x20         | 008 715 |
| 7        | Key of switch cabinet                 | 009 346        | 15  | Micro fuse F1,0A         | 008 748 |




## 16.2 Accessories part 2

| Pos      | Designation                        | Id             | Pos | Designation     | Id      |
|----------|------------------------------------|----------------|-----|-----------------|---------|
| <b>Σ</b> | <b>Accessories standard part 2</b> | <b>265 183</b> | 3   | Signal lightLED | 240 395 |
| 2        | Shim                               | 056 569        | 500 | Setscrew M16x40 | 244 061 |






## 17 Special attachments




### 17.1 Lateral yarn feeding

| Pos | Designation                                       | ID      | Pos | Designation                | ID                 |         |
|-----|---|---------|-----|----------------------------|--------------------|---------|
| Σ   | <b>Lateral yarn feeding on the left complete</b>  |         | 9   | <b>Yarn deflector</b>      |                    |         |
|     | E10–E18   | 264 319 |     | 9a                         | Support            | 264 456 |
|     | E7   E8   E6.2                                    | 270 426 |     | 9b                         | Axle               | 264 457 |
|     | E5  | 270 425 |     | 9c                         | Yarn Carriers MH 6 | 200 127 |
| Σ   | <b>Lateral yarn feeding on the right complete</b> |         | 10  | Cable AKF ADF XR161 left   | 264 028            |         |
|     | E10–E18   | 266 239 | 11  | Cable AKF ADF XR162 right  | 264 029            |         |
|     | E7   E8   E6.2                                    | 270 427 | 500 | Pan head screw M5x12       | 023 262            |         |
|     | E5  | 270 424 | 501 | Serrated lock washer J 5,3 | 022 489            |         |
| 1   | Safety door on the left complete                  | 263 320 | 502 | Cap screw M4x10            | 023 136            |         |
| 2   | Safety door on the right complete                 | 263 321 | 503 | Eyelet                     | 265 176            |         |
| 3   | <b>Left support complete</b>                      |         | 504 | Washer 4                   | 258 495            |         |
|     | E10–E18   | 263 305 | 505 | Hexagon nut M6             | 020 835            |         |
|     | E7   E8   E6.2                                    | 268 502 | 506 | O-ring 6x3                 | 022 856            |         |
|     | E5  | 268 491 |     |                            |                    |         |
| 4   | <b>Holder on the right complete</b>               |         |     |                            |                    |         |
|     | E10–E18   | 263 306 |     |                            |                    |         |
|     | E7   E8   E6.2                                    | 268 503 |     |                            |                    |         |
|     | E5  | 268 492 |     |                            |                    |         |




### 17.1.1 Safety door on the left

| Pos      | Designation                             | Id             | Pos | Designation             | Id      |
|----------|---|----------------|-----|-------------------------|---------|
| <b>Σ</b> | <b>Safety door on the left complete</b> | <b>263 320</b> |     |                         |         |
| 1        | Safety door on the left                 | 263 316        | 6   | Cover plate on the left | 264 027 |
| 2        | Hinge                                   | 263 216        | 500 | Screw 6x12              | 263 996 |
| 3        | Locking plate                           | 219 748        | 501 | Screw 50x20             | 263 540 |
| 4        | Actuator                                | 263 217        | 502 | Screw 4x16              | 263 995 |
| 5        | Cover plate                             | 263 980        | 503 | Screw 4x8               | 263 994 |




17.1.2 Safety door on the right

| Pos      | Designation                              | Id             | Pos | Designation              | Id      |
|----------|--|----------------|-----|--------------------------|---------|
| <b>Σ</b> | <b>Safety door on the right complete</b> | <b>263 321</b> |     |                          |         |
| 1        | Safety door on the right                 | 263 317        | 6   | Cover plate on the right | 264 560 |
| 2        | Hinge                                    | 263 216        | 500 | Screw 6x12               | 263 996 |
| 3        | Locking plate                            | 219 748        | 501 | Screw 50x20              | 263 540 |
| 4        | Actuator                                 | 263 217        | 502 | Screw 4x16               | 263 995 |
| 5        | Cover plate                              | 263 980        | 503 | Screw 4x8                | 263 994 |




### 17.1.3 Left yarn guide

| Pos      | Designation                  | ID                         | Pos | Designation                  | ID      |
|----------|------------------------------|----------------------------|-----|------------------------------|---------|
| <b>Σ</b> | <b>Left support complete</b> |                            |     |                              |         |
|          | E10-E18                      | 263 305                    | 7   | Yarn brake                   |         |
|          | E7   E8   E6.2               | 268 502                    |     | E10-E18                      | 259 440 |
|          | E5                           | 268 491                    |     | E5   E7   E8   E6.2          | 264 353 |
| 1        | Left support                 | 263 299                    | 8   | Thread clamp AKF             | 263 241 |
| 2        | Yarn tensioner complete      |                            | 9   | Cover cable AKF              | 263 493 |
|          | E10-E18                      | 263 294                    | 500 | Cable clip steel 4,8         | 258 495 |
|          | E7   E8   E6.2               | 268 504                    | 502 | Oval flange head screw M5x12 | 023 262 |
|          | E5                           | 267 535                    | 503 | Pan head screw M4x8          | 023 579 |
|          | 2a                           | Left fixation complete     | 504 | Pan head screw M5x8          | 239 408 |
|          | 501                          | Hexagon nut M5             | 505 | Cap screw M5x20              | 020 133 |
|          | 507                          | Serrated lock washer J 5,3 | 506 | Serrated lock washer J 4,3   | 022 482 |
| 4        | Yarn deflector complete      | 263 266                    | 508 | Eyelet 8                     | 021 504 |
| 5        | Distance bolt                | 263 302                    | 509 | Snap ring A 12               | 020 996 |
| 6        | Shaft                        | 263 301                    |     |                              |         |




17.1.4 Right yarn guide

| Pos      | Designation                   | ID                         | Pos     | Designation                  | ID                         |         |
|----------|-------------------------------|----------------------------|---------|------------------------------|----------------------------|---------|
| <b>Σ</b> | <b>Right support complete</b> |                            |         |                              |                            |         |
|          | E10–E18                       | 263 306                    | 7       | Yarn brake                   |                            |         |
|          | E7   E8   E6.2                | 268 503                    |         | E10–E18                      | 259 440                    |         |
|          | E5                            | 268 492                    |         | E5   E7   E8   E6.2          | 264 353                    |         |
| 1        | Right support complete        | 263 300                    | 8       | Thread clamp AKF             | 263 241                    |         |
| 2        | Yarn tensioner complete       |                            | 9       | Cover cable AKF              | 263 493                    |         |
|          | E10–E18                       | 263 294                    | 500     | Cable clip steel 4,8         | 258 495                    |         |
|          | E7   E8   E6.2                | 268 504                    | 502     | Oval flange head screw M5x12 | 023 262                    |         |
|          | E5                            | 267 535                    | 503     | Pan head screw M4x8          | 023 579                    |         |
|          | 2a                            | Left fixation complete     | 263 186 | 504                          | Pan head screw M5x8        | 239 408 |
|          | 501                           | Hexagon nut M5             | 020 835 | 505                          | Cap screw M5x20            | 020 133 |
|          | 507                           | Serrated lock washer J 5,3 | 022 489 | 506                          | Serrated lock washer J 4,3 | 022 482 |
| 4        | Yarn deflector complete       | 263 266                    | 508     | Eyelet 8                     | 021 504                    |         |
| 5        | Distance bolt                 | 263 302                    | 509     | Snap ring A 12               | 020 996                    |         |
| 6        | Shaft                         | 263 301                    |         |                              |                            |         |




## 17.1.5 Friction feed wheel complete

| Pos      | Designation                               | ID                            | Pos     | Designation                 | ID                   |         |
|----------|---|-------------------------------|---------|-----------------------------|----------------------|---------|
| $\Sigma$ | Friction feed wheel on the left complete  | 264 985                       | 4a      | Left support complete       | 265 152              |         |
|          | Friction feed wheel on the right complete | 264 986                       |         | Right support complete      | 265 153              |         |
| 1a       | Friction feed wheel on the left           | 269 403                       | 4b      | Support of left feed wheel  | 263 515              |         |
|          | Friction feed wheel on the right          | 269 398                       |         | Support of right feed wheel | 263 516              |         |
|          | 1b  | Three-phase AC motor complete | 219 800 | 5                           | Adaptor on the left  | 264 308 |
|          | 1c  | Micro Switches                | 008 664 |                             | Adaptor on the right | 264 309 |
| 2        | Friction roller complete                  | 269 400                       | 6       | Yarn guide rod complete     | 239431               |         |
| 3        | Ribbed V-belt V3J 406                     | 206 927                       | 500     | Screw KB40x25               | 241 595              |         |
|          |   |                               | 501     | Washer 4                    | 020 870              |         |
|          |   |                               | 502     | Cap screw M4x12             | 022 664              |         |
|          |   |                               | 900     | T-head bolt M8x25           | 022 866              |         |
|          |   |                               | 901     | Serrated nut M8-10          | 023 026              |         |
|          |   |                               | 902     | Cap screw M6x16             | 020 135              |         |




## 17.2 Storage feed wheel MSF-3 ADF

| Pos      | Designation                            | ID             | Note   |
|----------|--|----------------|--|
| <b>Σ</b> | <b>Assembly kit MSF-3 complete ADF</b> | <b>265 194</b> | Please order the MSF-3 spare parts at:<br>MEMMINGER-IRO GMBH<br>Jakob-Mutz-Strasse 7<br>D-72280 Dornstetten<br>Phone: +49 (0)7443 281-0<br>Fax: +49 (0)7443 281-101<br>The item no. and the designation for the MSF-3 spare parts can be found in the enclosed assembling instructions of the company MEMMINGER-IRO. |
| 1        | Transformer MSF-3 with cable           | 265 192        |  |
| 2        | Assembly kit MSF-3 without transformer | 265 193        |  |
| 2a       | Ribbon cable four-wire                 | 245 260        |  |
| 5*       | Storage feed wheel                     | 259 604        |  |




### 17.3 Yarn length measuring device on the left complete

| Pos      | Designation  | Id             | Pos | Designation                                  | Id      |
|----------|--|----------------|-----|--|---------|
| $\Sigma$ | <b>Yarn length measuring device on the left complete</b> | <b>265 546</b> | 9   | Operating instructions of ASCON ADF assembly | 265 567 |
| 1        | Yarn length measuring device on the left complete        | 257 283        | 500 | T-head bolt M8x25                            | 022 866 |
| 2        | Cable ASCON  | 257 239        | 501 | Serrated nut M8-10                           | 023 026 |
| 3        | Support on the left                                      | 265 543        | 502 | Cap screw M4x8                               | 022 501 |
| 4        | Connecting lug on the left                               | 257 137        | 503 | Cable tape 302x4,8                           | 008 642 |
| 5        | Adjustment weight  | 212 241        | 504 | Cap screw M5x12                              | 020 132 |
| 8        | DVD with operating instructions                          | 258 391        | 505 | Washer 5                                     | 020 871 |




17.3.1 Yarn length measuring device

| Pos      | Designation  | Id             | Pos | Designation                       | Id      |
|----------|--|----------------|-----|-----------------------------------|---------|
| <b>Σ</b> | <b>Yarn length measuring device on the left complete</b> | <b>257 283</b> | 8   | Yarn guide rod                    | 257 139 |
| 1        | Housing  | 257 281        | 9   | Card Ascon                        | 255 000 |
| 2        | Support  | 257 278        | 10  | Threaded strip                    | 257 138 |
| 3        | Cover  | 257 273        | 500 | Pan-head screw M5x10              | 023 247 |
| 4        | Fan with plug  | 257 048        | 501 | Screw 50x15                       | 251 728 |
| 5        | Protective grid fan Servo5                               | 229 142        | 502 | Sheet metal screw ST3,5x13        | 022 940 |
| 6        | Sensor   | 211 354        | 503 | Oval head screw with washer M3x10 | 023 380 |
| 6a       | Rubber running ring                                      | 258 582        | 504 | Spring nut M5                     | 022 873 |
| 7        | Sensor complete  | 212 406        | 505 | Serrated lock washer J3,7         | 022 554 |




## 17.4 Yarn length measuring device on the right complete

| Pos      | Designation   | Id             | Pos | Designation                                  | Id      |
|----------|---|----------------|-----|--|---------|
| $\Sigma$ | <b>Yarn length measuring device on the right complete</b> | <b>265 547</b> | 10  | Operating instructions of ASCON ADF assembly | 265 567 |
| 1        | Yarn length measuring device on the right complete        | 257 282        | 500 | T-head bolt M8x25                            | 022 866 |
| 2        | Cable ASCON   | 257 239        | 501 | Serrated nut M8-10                           | 023 026 |
| 3        | Support right   | 265 542        | 502 | Cap screw M4x8                               | 022 501 |
| 4        | Connecting lug on the right                               | 257 136        | 503 | Cable tape 302x4,8                           | 008 642 |
| 5        | Adjustment weight   | 212 241        | 504 | Cap screw M5x12                              | 020 132 |
| 8        | DVD with operating instructions                           | 258 391        | 505 | Washer 5                                     | 020 871 |




17.4.1 Yarn length measuring device on the right

| Pos      | Designation   | Id             | Pos | Designation                       | Id      |
|----------|---|----------------|-----|-----------------------------------|---------|
| <b>Σ</b> | <b>Yarn length measuring device on the right complete</b> | <b>257 282</b> | 8   | Yarn guide rod                    | 257 139 |
| 1        | Housing   | 257 281        | 9   | Card Ascon                        | 255 000 |
| 2        | Support   | 257 278        | 10  | Threaded strip                    | 257 138 |
| 3        | Cover   | 257 273        | 500 | Pan-head screw M5x10              | 023 247 |
| 4        | Fan with plug   | 257 048        | 501 | Screw 50x15                       | 251 728 |
| 5        | Protective grid fan Servo5                                | 229 142        | 502 | Sheet metal screw ST3,5x13        | 022 940 |
| 6        | Sensor  | 211 354        | 503 | Oval head screw with washer M3x10 | 023 380 |
| 6a       | Rubber running ring                                       | 258 582        | 504 | Spring nut M5                     | 022 873 |
| 7        | Sensor complete   | 212 406        | 505 | Serrated lock washer J3,7         | 022 554 |



## 17.5 Yarn brake

| Pos      | Designation       | ID             | Pos | Designation    | ID      |
|----------|-------------------|----------------|-----|----------------|---------|
| <b>Σ</b> | <b>Yarn brake</b> | <b>266 739</b> | 4   | Eyelet 8       | 021 504 |
| 1        | Support sheet     | 266 718        | 5   | Disk D = 130   | 263 545 |
| 2        | Yarn brake        | 259 440        | 6   | Snap ring A 12 | 020 996 |



## 17.6 Adjusting plates

| Pos       | Designation                             | Id             | Pos | Designation            | Id      |
|-----------|---|----------------|-----|------------------------|---------|
| <b>Σ1</b> | <b>Yarn carrier adjusting plate set</b> | <b>266 736</b> |     |                        |         |
| 12        | Adjusting plate E16-18                  | 265 064        | 17  | Adjusting plate V 0,25 | 267 253 |
| 13        | Adjusting plate E3-4                    | 265 061        | 18  | Adjusting plate V 0,5  | 258 199 |
| 14        | Adjusting plate E10-14                  | 265 063        | 19  | Adjusting plate V 1    | 258 200 |
| 15        | Adjusting plate E2,5.2-8                | 265 062        | 20  | Adjusting plate V 1,5  | 258 201 |

