



Yarn length measuring device on the left

Pos	Designation	Id	Pos	Designation	Id
Σ	Yarn length measuring device on the left complete	257 283	8	Yarn guide rod	257 139
1	Housing	257 281	9	Card Ascon	255 000
2	Support	257 278	10	Threaded strip	257 138
3	Cover	257 273	500	Pan-head screw M5x10	023 247
4	Ventilator with plug	257 048	501	Screw 50x15	251 728
5	Protective grid ventilator Servo5	229 142	502	Sheet metal screw ST3.5x13	022 940
6	Sensor	211 354	503	Oval head screw with washer M3x10	023 380
6a	Rubber running ring	258 582	504	Spring nut M5	022 873
7	Sensor complete	212 406	505	Serrated lock washer J3.7	022 554




Yarn length measuring device on the right

Pos	Designation	Id	Pos	Designation	Id
Σ	Yarn length measuring device on the right complete	257 282	8	Yarn guide rod	257 139
1	Housing	257 281	9	Card Ascon	255 000
2	Support	257 278	10	Threaded strip	257 138
3	Cover	257 273	500	Pan-head screw M5x10	023 247
4	Ventilator with plug	257 048	501	Screw 50x15	251 728
5	Protective grid ventilator Servo5	229 142	502	Sheet metal screw ST3.5x13	022 940
6	Sensor	211 354	503	Oval head screw with washer M3x10	023 380
6a	Rubber running ring	258 582	504	Spring nut M5	022 873
7	Sensor complete	212 406	505	Serrated lock washer J3.7	022 554




Yarn length measuring device on the left complete

Pos	Designation	Id	Pos	Designation	Id
Σ	Yarn length measuring device on the left complete	257 600			
1	Yarn length measuring device on the left complete	257 283	9	Holding plate	258 386
2	Cable ASCON	257 239	500	T-head bolt M8x25	022 866
3	Support on the left	257 122	501	Ribbed lock washer M8-10	023 026
4	Connecting lug on the left	257 137	502	Cap screw M4x8	022 501
5	Adjustment weight	212 241	503	Cable tape 92x2,4	008 642
6	Instructions ASCON	257 597	504	Cap screw M5x12	020 132
8	DVD with operating instructions	258 391	505	U-washer 5	020 871




Yarn length measuring device on the right complete

Pos	Designation	Id	Pos	Designation	Id
Σ	Yarn length measuring device on the right complete	257 599			
1	Yarn length measuring device on the right complete	257 282	9	Holding plate	258 386
2	Cable ASCON	257 239	500	T-head bolt M8x25	022 866
3	Support right	257 121	501	Ribbed lock washer M8-10	023 026
4	Connecting lug on the right	257 136	502	Cap screw M4x8	022 501
5	Adjustment weight	212 241	503	Cable tape 92x2,4	008 642
6	Instructions ASCON	257 597	504	Cap screw M5x12	020 132
8	DVD with operating instructions	258 391	505	U-washer 5	020 871



Yarn length measuring device on the right complete CMS 933

Pos	Designation	Id	Pos	Designation	Id
Σ	Yarn length measuring device on the left complete	257 903			
1	Yarn length measuring device on the left complete	257 283	9	Holding plate	258 386
2	Cable ASCON	257 239	500	T-head bolt M8x25	022 866
3	Support on the left	257 857	501	Ribbed lock washer M8-10	023 026
4	Connecting lug on the left	257 137	502	Cap screw M4x8	022 501
5	Adjustment weight	212 241	503	Cable tape 92x2,4	008 642
6	Instructions ASCON	257 597	504	Cap screw M5x12	020 132
8	DVD with operating instructions	258 391	505	U-washer 5	020 871



Yarn length measuring device on the right complete CMS 933

Pos	Designation	Id	Pos	Designation	Id
Σ	Yarn length measuring device on the right complete	257 904			
1	Yarn length measuring device on the right complete	257 282	9	Holding plate	258 386
2	Cable ASCON	257 239	500	T-head bolt M8x25	022 866
3	Support right	257 856	501	Ribbed lock washer M8-10	023 026
4	Connecting lug on the right	257 136	502	Cap screw M4x8	022 501
5	Adjustment weight	212 241	503	Cable tape 92x2,4	008 642
6	Instructions ASCON	257 597	504	Cap screw M5x12	020 132
8	DVD with operating instructions	258 391	505	U-washer 5	020 871

