Internal improvements

1 What is new in EKC V2.5?

Operating system of the machine: V_EKC_002.005.000_STOLL

Release: 08/2022


1.1 Internal improvements

Internal improvements and optimizations.

1.2 ADF - Double the quantity of yarn control units


i You can use this device independently of the operating system.

For the coarser ADF machines (E5 - E8) is a second yarn guide device available.



This special attachment (ID 283 754) consists of:

- Yarn guide device
- 32 Yarn control units (ID 270 467)
- 2 supports for the yarn guide device
- Connection cable for the yarn control units




EN 1



1.3 ADF - Narrow yarn carrier tip E14 - E20

i You can use this device independently of the operating system.

For the plating is a narrow yarn carrier tip available. A yarn carrier can then be adjusted lower, for example with Devoré and ikat plating.




Comparison of "Narrow and standard yarn carrier tip"

There are two yarn carrier bows with narrow yarn carrier tip available:


Yarn carrier bow for yarn carrier 1A, 2B	281 757
Yarn carrier bow for yarn carrier 1B, 2A	281 758

Exchange the yarn carrier bow of an available yarn carrier with the yarn carrier bow with narrow yarn carrier tip.



2 EN





The narrow yarn carrier tips can be used with the following gauges:

- E 14, E16, E18, E20
- E7.2, E8.2, E10.2

Important:

Check the setting of the needle brushes

The needle brushes have to be adjusted correctly, so that the needle latches open safely. Otherwise, there is a risk that the yarn carrier damages the needle latches.

EN 3